



Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window



△數		訂正事項		擔當		檢圖		年月日		△數		訂正事項		擔當		檢圖		年月日		
COUNT		DISCRIPTION OF REVISIONS		B Y		CHKD		DATE		COUNT		DISCRIPTION OF REVISIONS		B Y		CHKD		DATE		
△									.	.	△								.	.
△									.	.	△								.	.
△									.	.	△								.	.

RECOMMENDED PCB LAYOUT(Top-View)



NOTE

- SOLDERING TEMPERATURE : 250°C PEAK, 10sec MAX.
- OPERATING TEMPERATURE : -55°~105°C
- USED REFLOW SYSTEM : IN THE AIR OR NITROGEN
- NO. OF CYCLES : 2 MAX
- MATING PART
FEMALE : DF51K-2S-2C
- CO-PLANARITY : 0.12 MAX.
- RECOMMENDED PCB THICKNESS IS 1.6mm.
- RECOMMENDED SOLDER THICKNESS IS 0.15mm
- UL(File No. E132750) AUTHORIZATION ARTICLE.
C-UL(File No. E132750) AUTHORIZATION ARTICLE.




4	LCP	BLACK	8	PS	REEL BOBBIN
3	BRASS	TIN PLATED : 1μm MIN UNDER PLATING : NICKEL 1μm MIN	7	PET	COVER TAPE
2	BRASS	CONTACT AREA : GOLD 0.1μm MIN SMT LEAD : GOLD 0.05μm MIN UNDER PLATING : NICKEL 1μm MIN	6	CONNECTOR	DF51K-2P-2V
1	LCP	BLACK	5	PS	EMBOSS CARRIER TAPE
NO.	MATERIAL	FINISH,REMARKS	NO.	MATERIAL	FINISH,REMARKS

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	CHO 22.04.20 J.S	CHO 22.04.20 J.S	LIM 22.04.20 S.M	LIM 22.04.20 S.M	ENG 2023.07.24 DEPT
SCALE 4:1 UNITS mm	DRAWING NO. EDC3-633513	PART NO. DF51K-2P-2V(805)	CODE NO. CL 6652-0074-5-805	1 2	


Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window


PACKING STYLE

PACKING STYLE DRAWING



REEL DIMENSION (FREE)



 SCALE 4:1 UNITS mm	DRAWING NO. EDC3-633513		PART NO. DF51K-2P-2V(805)	
	 HIROSE KOREA CO.,LTD.		CODE NO. CL 6652-0074-5-805	
			2/2	