


May.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△						△					
△						△					
<b>APPLICABLE STANDARD</b>											
RATING	OPERATING TEMPERATURE RANGE		-40°C ~ + 105°C			STORAGE TEMPERATURE RANGE		-40°C ~ +105°C			
	CURRENT		1A			APPLICABLE CABLE		-			
<b>SPECIFICATIONS</b>											
ITEM		TEST METHOD				REQUIREMENTS				QT	AT
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT CONFIRMED VISUALLY				According To Drawing				0	0
<b>ELECTRICAL CHARACTERISTICS</b>											
Contact resistance		Open circuit voltage is AC 20mV, 1kHz Short circuit current is AC 10mA				Initial : 50mΩ Max After : 100mΩ Max				0	-
Insulation resistance		Mate applicable connector and apply a voltage of DC 500 V.				Initial : 100MΩ Min. After : 100MΩ Min.				0	-
Voltage proof		Mate applicable and apply a voltage of AC 500V for 1 min.				No dielectric breakdown.				0	-
<b>MECHANICAL CHARACTERISTICS</b>											
Mechanical operation		10 times, 50 times, and 100 times at a rate of 600 times or less per hour.				① No Damage, Crack And Looseness Of Parts. ② Contact resistance : 100mΩ Max ③ Insulation resistance : 100MΩ Min. ④ Voltage proof No dielectric breakdown.				0	-
Shock		3 both axial directions, 10 times each, 60 times(Acceleration : 500 m/s <sup>2</sup> Duration : 10ms)				① No Damage, Crack And Looseness Of Parts. ② Contact resistance : 100mΩ Max ③ No Electrical discontinuity of 10μs.				0	-
Vibration Resistance		Frequency 5 to 600Hz, acceleration of 73m/s <sup>2</sup> , full amplitude of 16.5mm, in 3 axis directions for 8 hours.				① No Damage, Crack And Looseness Of Parts. ② Contact resistance : 100mΩ Max ③ No Electrical discontinuity of 10μs.				0	-
Locking Force		Apply a force of 100N or less in the direction of the mate axis.				① Be fully assembled. ② No problems after assembly.				0	-
<b>ENVIRONMENTAL CHARACTERISTICS</b>											
Rapid change of temperature		Temperature : -40±2°C → +105±2°C Time : 30min → 30min Above conditions repeated for 500 cycles				① No Damage, Crack And Looseness Of Parts. ② Contact resistance : 100mΩ Max ③ Insulation resistance : 100MΩ Min.				0	-
Damp heat (Steady state)		Exposed at 85±2°C, 95%, 240Hr				① No Damage, Crack And Looseness Of Parts. ② Contact resistance : 100mΩ Max ③ Insulation resistance : 100MΩ Min.				0	-
Dry heat		Exposed at 85°C, 105°C, 125°C, 24Hr, 120Hr, 200Hr, 300Hr, 500Hr, 1,000Hr				① No Damage, Crack And Looseness Of Parts. ② Contact resistance : 100mΩ Max				0	-
Cold		Exposed at -40±2°C, 120Hr				① No Damage, Crack And Looseness Of Parts. ② Contact resistance : 100mΩ Max				0	-
Corrosion Gas		H <sub>2</sub> S : 10±5 ,NO <sub>2</sub> : 200±5, Cl <sub>2</sub> : 10±5, SO <sub>2</sub> : 200±5 (Unit : ppb) Expose at 21days				① No Damage, Crack And Looseness Of Parts. ② Contact resistance : 100mΩ Max				0	-
<b>REMARKS</b>											
<b>CONDITIONS FOR TESTING</b>					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED		
* Note (Note1)Including temperature rise by conducting					S.J MOON 24.10.23	S.J MOON 24.10.23	B.H AN 24.10.23	B.H AN 24.10.23			
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST O: APPLICABLE TEST											
HIROSE KOREA CO.,LTD.			SPECIFICATION SHEET				PART NO. KMA01-4DP-4.5DS/B(800)				
CODE NO.(OLD) CL			DRAWING NO. ELC3-634349-00			CODE NO. CL 6482-0019-2-800			1/1		