


	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE												
△						△																	
△						△																	
APPLICABLE STANDARD																							
RATING	Operating Temperature Range		-55℃ to +105℃ (Note1)			Storage Temperature Range		-10℃ to +60℃ (Note3)															
	Operating Humidity Range		20% to 80% (Note2)			Storage Humidity Range		40% to 70% (Note3)															
	Applicable Connector		DF51K#-24DP-2DSA/DS (###)			Voltage		250V AC/DC															
	Applicable Contact		DF51K-22SC(A)/SCF(A) (###) DF51K-2428SC(A)/SCF(A) (###) DF51K-30SC(A)/SCF(A) (###)			Current		AWG 30: 0.5A AWG 28: 1A AWG 26: 1.5A AWG 22-24: 2A															
SPECIFICATIONS																							
ITEM		TEST METHOD				REQUIREMENTS			QT	AT													
CONSTRUCTION																							
General Examination		Visually and by measuring instrument.				According to drawing.			0	0													
Marking		Confirmed visually.							0	0													
ELECTRICAL CHARACTERISTICS																							
Contact Resistance		20mV MAX, 1mA (DC or 1000Hz).				30 mΩ MAX.			0	-													
Millivolt Level Method																							
Insulation Resistance		500 V DC.				1,000 MΩ MIN.			0	-													
Voltage Proof		650 V AC for 1 min.				No flashover or breakdown.			0	-													
MECHANICAL CHARACTERISTICS																							
Mechanical Operation (Sn Plating)		30 times insertion and extraction.				①Contact resistance: 30mΩ MAX ②No damage, crack or looseness of parts.			0	-													
Mechanical Operation (Au Plating)		50 times insertion and extraction.				①Contact resistance: 30mΩ MAX ②No damage, crack or looseness of parts.			0	-													
Mating and unmating Force (Sn Plating)		It takes out and inserts with a conformity connector.				①Insertion Force: 104.2N MAX ②Extraction Force: 6.2N MIN			0	-													
Mating and unmating Force (Au Plating)		It takes out and inserts with a conformity connector.				①Insertion Force: 66.2N MAX ②Extraction Force: 6.0N MIN			0	-													
Vibration		Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 10 cycles for 3 direction.				①No electrical discontinuity of 1 μ s. ②No damage, crack or looseness of parts.			0	-													
Shock		Acceleration 490 m/s ² duration of pulse 11 ms at 3 times for 3 directions.							0	-													
Contact extraction force		Pull out the cable after housing fixation.				11.8N MIN			0	-													
ENVIRONMENTAL CHARACTERISTICS																							
Damp Heat (Steady State)		Exposed at 40 ± 2 °C , humidity 90 to 95 %, 96 h. (After leaving the room temperature for 1 to 2h.)				①Contact resistance: 30 mΩ MAX. ②Insulation resistance: 500MΩ MIN. ③No damage, crack or looseness of parts.			0	-													
Rapid Change of Temperature		Temperature -55 °C → +105 °C Time 30min → 30min Under 5 Cycles. (The transferring time of the tank is 2 to 3 MIN) (After leaving the room temperature for 1 to 2h.)				①Contact resistance: 30 mΩ MAX. ②Insulation resistance: 1,000MΩ MIN. ③No damage, crack or looseness of parts.			0	-													
Dry Heat		Exposed at 105±2 °C, 96h							0	-													
Cold		Exposed at -55±3 °C, 96h							0	-													
Remarks																							
Note 1: Include the temperature rising by current.																							
Note 2: No condensing																							
Note 3: Apply to the condition of long term storage for unused products before pcb on board, after pcb board , operating temperature and humidity range is applied for interim storage during transportation.																							
					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED														
					J.S CHOI	J.S CHOI	S.M.LIM	T.S KANG															
					17.12.22	17.12.22	17.12.22	17.12.22															
Unless otherwise specified, refer to IEC 60512.																							
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST O: APPLICABLE TEST																							
HIROSE KOREA CO.,LTD.				SPECIFICATION SHEET			PART NO. DF51K-24DS-2C (800)																
CODE NO.(OLD) CL			DRAWING NO. ELC4-632493			CODE NO. CL 6652-0035-3-800			1/1														