


CALUS



Technical drawing of a mechanical part with dimensions and callouts:

- Horizontal dimension: 8.75 ± 0.3
- Horizontal dimension: 3 ± 0.3
- Vertical dimension: 9.45 ± 0.3
- Vertical dimension: 2 ± 0.2
- Callout 1 points to the left vertical edge.
- Callout 2 points to the bottom right corner.

Technical drawing of a mechanical part with dimensions and tolerances:

- Overall width: 7.14 ± 0.1
- Overall height: 4 ± 0.1
- Top surface width: $P = 2 \pm 0.05$
- Left hole diameter: $\varnothing 1.7 \pm 0.1$
- Left hole position from bottom: 2.7 ± 0.1
- Right hole diameter: $\varnothing 0.8 \pm 0.1$
- Right hole position from bottom: 2.7 ± 0.1
- Bottom surface width: 2 ± 0.05

