

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C (NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C (NOTE3)		
	OPERATING HUMIDITY RANGE	20 % TO 80 % (NOTES 2)	STORAGE HUMIDITY RANGE	40 % TO 70 % (NOTE3)		
	VOLTAGE	150 V AC (DC)	CURRENT	1 A		
	APPLICABLE CONNECTOR	DF13-3S-1.25C	APPLICABLE CONTACT	DF13(G)-2630SCF DF13-3032SCF		
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.			X	X
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		100 m A (DC OR 1000 Hz).		30 mΩ MAX.	X	—
INSULATION RESISTANCE		100 V DC.		500 MΩ MIN.	X	—
VOLTAGE PROOF		500 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS						
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			X	—
ENVIRONMENTAL CHARACTERISTICS						
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→ 15 TO 35→+85→ 15 TO 35 °C TIME 30→ 2 TO 3→30→ 2 TO 3 min. UNDER 5 CYCLES.		① CONTACT RESISTANCE: 30mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.			X	—
RESISTANCE TO SOLDERING HEAT		1) REFLOW SOLDERING «REFLOW AREA» 250°C MAX 10 sec MAX 230°C MIN 60 sec MAX «PREHEATING AREA» 170°C TO 190°C 60 sec TO 120 sec PUT THROUGH IN REFLOW FURNACE TWICE, LEAVE IN AMBIENT TEMPERATURE AND HUMIDITY FOR 1 HOUR. 2) MANUAL SOLDERING SOLDERING IRON TEMPERATURE :350°C, SOLDERING TIME : 3sec. NO STRENGTH ON CONTACT.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 245°C FOR INSERTION DURATION, 3sec.		SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSSED.	X	—
REMARKS						
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT						
NOTE2:NO CONDENSING						
NOTE3:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD, AFTER PCB BOARD , OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION.						
Unless otherwise specified, refer to JIS C 5402.						
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
△						
			APPROVED	HK. UMEHARA	11. 09. 22	
			CHECKED	HK. UMEHARA	11. 09. 22	
			DESIGNED	HT. SATO	11. 09. 22	
			DRAWN	MI. SAKIMURA	11. 09. 20	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-083459-01	
HRS	SPECIFICATION SHEET		PART NO.	DF13A-3P-1. 25H (71)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL536	△	1/1