

May.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

| COUNT | DESCRIPTION OF REVISIONS | BY | CHKD | DATE | COUNT | DESCRIPTION OF REVISIONS | BY | CHKD | DATE |
|---|-----------------------------|---|------|------|---|--------------------------|---------------|-----------------------------|-----------------------|
| △ | | | | | △ | | | | |
| △ | | | | | △ | | | | |
| APPLICABLE STANDARD | | | | | | | | | |
| RATING | OPERATING TEMPERATURE RANGE | -35 °C TO +85 °C(NOTE1) | | | STORAGE TEMPERATURE RANGE | -10 °C TO +60 °C | | | |
| | VOLTAGE | 150 V AC | | | APPLICABLE CONTACT | — | | | |
| | CURRENT | 1 A | | | APPLICABLE CONNECTOR | DF13-*DP-1.25C | | | |
| | | | | | APPLICABLE CABLE | — | | | |
| SPECIFICATIONS | | | | | | | | | |
| ITEM | | TEST METHOD | | | REQUIREMENTS | | | QT | AT |
| CONSTRUCTION | | | | | | | | | |
| GENERAL EXAMINATION | | VISUALLY AND BY MEASURING INSTRUMENT. | | | ACCORDING TO DRAWING. | | | <input type="radio"/> | <input type="radio"/> |
| MARKING | | CONFIRMED VISUALLY. | | | | | | <input type="radio"/> | <input type="radio"/> |
| ELECTRIC CHARACTERISTICS | | | | | | | | | |
| CONTACT RESISTANCE | | 100 mA (DC OR 1000 Hz). | | | 30 mΩ MAX. | | | <input type="radio"/> | — |
| CONTACT RESISTANCE MILLIVOLT LEVEL METHOD | | 20 mV MAX, mA(DC OR 1000 Hz). | | | | | | — | — |
| INSULATION RESISTANCE | | 100 V DC. | | | 500 MΩ MIN. | | | <input type="radio"/> | — |
| VOLTAGE PROOF | | 500 V AC FOR 1 min. | | | NO FLASHOVER OR BREAKDOWN. | | | <input type="radio"/> | — |
| MECHANICAL CHARACTERISTICS | | | | | | | | | |
| CONTACT INSERTION AND EXTRACTION FORCES | | <input type="checkbox"/> 0.35±0.002 BY STEEL GAUGE. | | | INSERTION FORCE 3.9 N MAX. EXTRACTION FORCE 0.3 N MIN. | | | <input type="radio"/> | — |
| INSERTION AND WITHDRAWAL FORCES | | MEASURED BY APPLICABLE CONNECTOR. | | | INSERTION FORCE _____ N MAX. EXTRACTION FORCE _____ N MIN. | | | — | — |
| MECHANICAL OPERATION | | 30 TIMES INSERTIONS AND EXTRACTIONS. | | | ① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS. | | | <input type="radio"/> | — |
| VIBRATION | | FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, - m/s ² AT 2 h, FOR 3 DIRECTIONS. | | | ① NO ELECTRICAL DISCONTINUITY OF 1 μs. | | | <input type="radio"/> | — |
| SHOCK | | 490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS. | | | ② CONTACT RESISTANCE: - mΩ MAX. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS. | | | <input type="radio"/> | — |
| ENVIRONMENTAL CHARACTERISTICS | | | | | | | | | |
| RAPID CHANGE OF TEMPERATURE | | TEMPERATURE -55 → 5 ~ 35 → +85 → 5 ~ 35 °C TIME 30 → 10 → 30 → 10 min UNDER 5 CYCLES. | | | ① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS. | | | <input type="radio"/> | — |
| DAMP HEAT (STEADY STATE) | | EXPOSED AT 40 ± 2 °C, 90 ~ 95 %, 96 h. | | | ① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS. | | | <input type="radio"/> | — |
| RESISTANCE TO SOLDERING HEAT | | SOLDER TEMPERATURE, °C, FOR IMMERSION, DURATION, s. | | | NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS. | | | — | — |
| SOLDERABILITY | | SOLDERED AT SOLDER TEMPERATURE, °C FOR IMMERSION DURATION, s. | | | SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED. | | | — | — |
| REMARKS NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT. | | | | | DRAWN | DESIGNED | CHECKED | APPROVED | RELEASED |
| | | | | | <i>H. Umehara</i> | <i>H. Umehara</i> | <i>J. Ona</i> | <i>M. Yamamoto</i> | |
| Unless otherwise specified, refer to MIL-STD-1344. | | | | | 197.3.3 | 197.3.3 | 97.3.4 | 97.3.4 | |
| Note QT:Qualification Test AT:Assurance Test ○:Applicable Test | | | | | | | | | |
| HS HIROSE ELECTRIC CO., LTD. | | | | | SPECIFICATION SHEET | | | PART NO. DF13-*DS*-1.25C | |
| CODE NO.(OLD) CL | | DRAWING NO. ELC4-160109-03 | | | PART NO. CL | | 536 | | 1/1 |



TO