







RECOMMENDED PCB LATOUT (Top-View)



MATING FIGURE



NOTE

1. LEAD CO-PLANARITY SHALL BE 0.1mmMAX
2. 1REEL : 1,500EA CONNECTORS
3. UL(File No. E132750) AUTHORIZATION ARTICLE.
C-UL(File No. E132750) AUTHORIZATION ARTICLE.



3	COPPER ALLOY	CONTACT AREA : GOLD 0.76µm MIN. SMT LEAD : GOLD 0.05µm MIN. △ UNDER PLATING : NICKEL 1.27µm MIN.	6	CONNECTOR	KW30-6S-1H
2	PHOSPHOR BRONZE	Sn PLATED	5	PET	COVER TAPE
1	LCP	UL94-V0, BLACK	4	PS	EMBOSS CARRIER TAPE
NO.	MATERIAL	FINISH,REMARKS	NO.	MATERIAL	FINISH,REMARKS
CODE NO. (OLD)			DRAWN	DESIGNED	CHECKED
			SHIN 21.08.27 J.H	SHIN 21.08.27 J.H	LIM 21.08.27 S.M
DRAWING NO.			PART NO.		
EDC3-632848			KW30-6S-1H (805)		
CODE NO			CODE NO		
CL 6669-0001-3-805			1 1		