


Apr.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



△數 COUNT	訂正事項 DESCRIPTION OF REVISIONS	擔當 B Y	檢圖 CHKD	年月日 DATE	△數 COUNT	訂正事項 DESCRIPTION OF REVISIONS	擔當 B Y	檢圖 CHKD	年月日 DATE
△					△				
△					△				
△					△				


HRS DRAWING FOR REFERENCE

- NOTE
1. ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX.
  2. CONTACT PLATING SPECIFICATIONS.  
CONTACT AREA : GOLD  $0.05 \mu\text{m}$  MIN.  
SMT LEAD : GOLD  $0.05 \mu\text{m}$  MIN.  
UNDER PLATING : NICKEL  $1 \mu\text{m}$  MIN.  
( SURFACE : SEALING )
  3. METAL FITTING PLATING SPECIFICATIONS.  
SMT LEAD : GOLD  $0.05 \mu\text{m}$  MIN.  
UNDERPLATING : NICKEL  $1 \mu\text{m}$  MIN.  
( SURFACE : SEALING )
  4. HRS MARK AND CAV No. ARE INDICATED IN APPROX POSITION SHOWN.
  5. A PART OF THE WALL COULD BE NOTCHED.

4	PS	CLEAR (EMBOSSED CARRIER TAPE)								
3	COPPER ALLOY	3	7	PS	CLEAR (REINFORCEMENT COLLAR)					
2	COPPER ALLOY	2	6	PS	BLACK (PLASTIC REEL)					
1	LCP	UL94 V-0, BLACK	5	POLYESTER	CLEAR (COVER TAPE)					
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS					
REMARKS						DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
						W. Y. AHN	W. Y. AHN	G. O. LEE	H. W. JO	24.07.16
						24.07.16	24.07.16	24.07.16	24.07.16	
CODE NO. (OLD)	DRAWING NO. EDC3-633124-95		PART NO. BM23PF0.8-60DP-0.35V(895)							
SCALE 10:1	HRS HIROSE KOREA CO., LTD.		CODE NO. CL 6644-0068-8-895			1/3				
UNITS mm										


Apr.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

7 RECOMMENDED PCB LAYOUT




RECOMMENDED METAL MASK DIMENSIONS

METAL MASK THICKNESS : 100 μm



6 RECOMMENDED REFLOW TEMPERATURE PROFILE USING LEAD-FREE SOLDER PASTE.




REFLOW METHOD: N<sub>2</sub> REFLOW  
 NUMBER OF REFLOW CYCLES: 2 CYCLES MAX.  
 1) REFLOW TIME  
 DURATION ABOVE 220°C, 60 SEC MAX.  
 (PEAK TEMPERATURE: 250°C MAX)  
 2) PRE-HEAT TIME  
 PRE-HEAT TEMPERATURE(MIN): 150°C  
 PRE-HEAT TEMPERATURE(MAX): 180°C  
 PRE-HEAT TIME: 90-120 SEC.

- 6 THIS TEMPERATURE PROFILE IS PER THE CONDITIONS SHOWN ABOVE. ADDITIONAL FACTORS, SUCH AS SOLDER PASTE TYPE, PCB SIZE AND OTHER MOUNTED COMPONENTS COULD AFFECT THE PROFILE. THEREFORE, A THOROUGH EVALUATION OF MOUNTING CONDITION IS REQUIRED PRIOR TO PRODUCTION. TEMPERATURE IS MEASURED AT CONTACT LEAD.
- 7 PLEASE CONTACT US IN CASE YOU WILL MAKE DIFFERENT SETTINGS FROM OUR RECOMMENDATION.


 SCALE 10:1 UNITS mm	DRAWING NO.	EDC3-633124-95	PART NO.	BM23PF0.8-60DP-0.35V(895)
	HIROSE KOREA CO., LTD.		CODE NO.	CL 6644-0068-8-895

Apr.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


# EMBOSED CARRIER TAPE PACKAGING (5:1)




B-B (5:1)




10 TAPING (FREE)




C-C (5:1)




D (10:1)



## STYLE AND DIMENTION OF REEL (FREE)



E-E (FREE)



### DETAIL OF PART No. LABEL

SUPPLIER	
QUANTITY	
PART NO.	
CODE NO.	
DATE OF MANUFACTURED	
生産月日	年 月 日
図番	** ** *
品名	BM23PF0.8-60DP-0.35V(895)
納入数量	1,000個
納入者	HIROSE KOREA

8 . PER REEL 1,000 CONNECTORS.

9 . THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

10 REFER TO JIS C 0806, IEC-60286-3 (PACKAGING OF COMPONENTS FOR AUTOMATIC HANDLING)

11 AFTER PACKAGING, ROLL 2 METERS OF THE REINFORCEMENT COLLAR TO OUTER CIRCUMFERENCE OF TAPE AND REEL POCKET. AND TAPE DOWN AT THE END THE COLLAR.

	DRAWING NO.	EDC3-633124-95	PART NO.	BM23PF0.8-60DP-0.35V(895)
	SCALE	10:1	CODE NO.	CL 6644-0068-8-895
UNITS	HRS HIROSE KOREA CO., LTD.			3/3