

Jul.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				
APPLICABLE STANDARD									
RATING	VOLTAGE	250V AC			CURRENT	3A			
	OPERATING TEMPERATURE RANGE	-35 °C TO +85 °C(NOTE1)			STORAGE TEMPERATURE RANGE	-10°C TO +60 °C(NOTE3)			
	OPERATING HUMIDITY RANGE	20% TO 80%(NOTE2)			STORAGE HUMIDITY RANGE	20% TO 70%(NOTE3)			
	APPLICABLE CONNECTOR	DF1B-*S-2.5R							
SPECIFICATIONS									
ITEM		TEST METHOD			REQUIREMENTS			QT	AT
CONSTRUCTION									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.			×	×
MARKING		CONFIRMED VISUALLY.						×	×
ELECTRIC CHARACTERISTICS									
CONTACT RESISTANCE		100mA (DC OR 1000 Hz).			30mΩ MAX.			×	—
INSULATION RESISTANCE		500V DC.			1000MΩ MIN.			×	—
VOLTAGE PROOF		650V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN.			×	—
MECHANICAL CHARACTERISTICS									
CONTACT INSERTION AND EXTRACTION FORCES		□0.635±0.002 BY STEEL GAUGE.			INSERTION FORCE 4.4N MAX EXTRACTION FORCE 0.4N MIN			×	—
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.			① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			×	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 1μs.			×	—
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			×	—
ENVIRONMENTAL CHARACTERISTICS									
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.			① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			×	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 →5 TO 35 →+85→5 TO35°C TIME 30 →10 TO 15 →30 →10 TO15min UNDER 5 CYCLES.			① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			×	—
REMARKS									
NOTE1:INCLUDING THE TEMPERATURE RISE BY CURRENT. NOTE2:NO CONDENSING. NOTE3:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD, AFTER PCB BOARD, OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION. Unless otherwise specified, refer to JIS C 5402					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
					T. Kumogawa '04.03.05	T. Kumogawa '04.03.05	T. Miyajahi '04.03.08	J. Ona 04.03.09	
Note QT:Qualification Test AT:Assurance Test ×:Applicable Test									
HRS HIROSE ELECTRIC CO., LTD.					SPECIFICATION SHEET			PART NO. DF1B-*P-2.5DS(01)	
CODE NO.(OLD) CL			DRAWING NO. ELC4-162412-01			PART NO. CL541			1/1

TO

