

APPLICABLE STANDARD					
RATING	VOLTAGE	250 V AC /DC	CURRENT	AWG24 : 3 A AWG26 : 2 A AWG28 : 1 A	
	OPERATING TEMPERATURE RANGE	-35 °C TO +85 °C(NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60 °C(NOTE 3)	
	OPERATING HUMIDITY RANGE	40% TO + 80%(NOTE 2)	STORAGE HUMIDITY RANGE	40% TO + 70%(NOTE 3)	
	APPLICABLE CABLE	UL1007,1061 : 24-28 AWG	APPLICABLE CONNECTOR	DF1B-*S-2.5R DF1B-*DS-2.5RC DF1B-*(D)ES-2.5RC	
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.			X	X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	100 mA (DC OR 1000Hz).		30 mΩ MAX.	X	—
MECHANICAL CHARACTERISTICS					
CONTACT INSERTION AND EXTRACTION FORCE	□0.635±0.002mm BY STEEL GAUGE.		INSERTION FORCE : 4.4 N MAX. EXTRACTION FORCE : 0.44 N MIN.	X	—
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.				
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→5 TO 35→+85→5 TO35 °C TIME 30 →5 →30 →5 min UNDER 5 CYCLES.		① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.		① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
REMARKS					
NOTE 1:INCLUDING THE TEMPERATURE RISING BY CURRENT NOTE 2:NO CONDENSING. NOTE 3:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE MOUNTED ON PCB, AFTER MOUNTED ON PCB, OPERATINGTEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION.					
△	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
Unless otherwise specified, refer to IEC 60512.			APPROVED	HS. OKAWA	20181023
			CHECKED	SZ. ONO	20181023
			DESIGNED	TS. KUMAZAWA	20181023
			DRAWN	SN. MIWA	20181023
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-080530-00-00
HRS	SPECIFICATION SHEET		PART NO.	DF1B-2428SCF	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL541-0678-1-00	△ 1/1