

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				

APPLICABLE STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-35 °C TO 85 °C(NOTE 1)				STORAGE TEMPERATURE RANGE	-10°C TO 60 °C		
	VOLTAGE	250 V AC				APPLICABLE CONNECTORS	DF1B- * S-2.5R DF1B- * DS-2.5RC DF1B- * (D)ES-2.5RC		
	CURRENT	AWG24~28 : 1A				OPERATING HUMIDITY RANGE	UL1007,1061:AWG24~28		

SPECIFICATIONS						
ITEM	TEST METHOD	REQUIREMENTS	QT	AT		
CONSTRUCTION						
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×		
MARKING	CONFIRMED VISUALLY.		×	×		
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD.	20 mV MAX, 1 mA(DC OR 1000 Hz).	30 mΩ MAX.	×	—		
INSULATION RESISTANCE	500 V DC.	1000 MΩ MIN.	×	—		
VOLTAGE PROOF	650 V AC FOR 1 min.	NO FLASH OVER OR BREAKDOWN.	×	—		
MECHANICAL CHARACTERISTICS						
CONTACT INSERTION AND EXTRACTION FORCES	□0.635±0.002 BY STEEL GAUGE.	INSERTION FORCE 4.4 N MAX. EXTRACTION FORCE 0.44 N MIN.	×	—		
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	×	—		
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75mm AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② CONTACT RESISTANCE: 30 mΩ MAX.	×	—		
SHOCK	490 m/s ² DIRECTIONS OF PULSE 11 ms AT 3 TIME FOR 3 DIRECTION.	③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	×	—		
ENVIRONMENTAL CHARACTERISTICS						
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 →5 TO 35→85 →5 TO 35 °C TIME 30 → 10 → 30 → 10 min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE:1000MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	×	—		
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 TO 95 %, 96 h.	① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 1000MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	×	—		
REMARKS NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT		DRAWN Y.INOUE	DESIGNED Y.Inoue	CHECKED J.Miyazaki	APPROVED K.Katayama	RELEASED
Unless otherwise specified, refer to MIL-STD-1344.		'00.09.14	'00. 9.14	'00. 9.14	'00.9.18	
Note QT: Qualification Test AT: Assurance Test ×:Applicable Test						
HRS HIROSE ELECTRIC CO., LTD.		SPECIFICATION SHEET		PART NO. DF1B-2428SCFA		
CODE NO.(OLD) CL	DRAWING NO. ELC4-080532	PEART NO CL541-0680-3		1/1		