Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	VOLTAGE	150V AC	CURRENT	1A
	OPERATING TEMPERATURE RANGE	-35°C TO + 85°C(NOTE 1)	STORAGE TEMPERATURE RANGE	-10°C TO + 60°C(NOTE 3)
	OPERATING HUMIDITY RANGE	40% TO 80%(NOTE 2)	STORAGE HUMIDITY RANGE	40% TO 70%(NOTE 3)
	APPLICABLE CONNECTOR	DF13-*S-1.25C	APPLAICABLE CRIMP CONTACT	DF13-2630SCFA, DF13-3032SCFA

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	100m A (DC OR 1000 Hz).	30mΩ MAX.	X	—
INSULATION RESISTANCE	100V DC.	500MΩ MIN.	X	—
VOLTAGE PROOF	500V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	50TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	–
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	–
SHOCK	490 m/s^2 DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	–
ENVIRONMENTAL CHARACTERISTICS				
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→ 5 TO 35→85→ 5 TO 35 °C TIME 30→ 5 TO 15 →30→ 5 TO 15 min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 30mΩ MAX. ② INSULATION RESISTANCE: 500MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	–
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	① CONTACT RESISTANCE: 30mΩ MAX. ② INSULATION RESISTANCE: 500MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	–
RESISTANCE TO SOLDERING HEAT	1) FLOW SOLDERING 250±5℃MAX, FOR 3 SECONDS. 2) SOLDERING IRONS: :290±10℃, FOR 3 SECONDS .	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	–
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 215±5°C FOR INSERTION DURATION, 3 SECONDS.	SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	X	–

REMARKS
NOTE 1:INCLUDING THE TEMPERATURE RISE BY CURRENT.
NOTE2:NO CONDENSING.
NOTE3:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD AFTER PCBBOARD , OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERM STORAGE DURING TRANSPORTATION.

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△0					

Unless otherwise specifid , refer to JIS C 5402.

APPROVED	TS. SAKATA	08.11.17
CHECKED	TS. KUMAZAWA	08.11.14
DESIGNED	SN. KOBAYASHI	08.11.12
DRAWN	YK. NAKATSU	08.11.10

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

DRAWING NO. ELC4-162420-04

HRS	SPECIFICATION SHEET	PART NO.	DF13-*P-1.25DS(50)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL536 △0	1/1

FORM HD0011-2-1