






CODE No.	CONTACT	A	B	C	D	E	F
CL537-0592-0-51	20	7.2	4.5	5.3	5.7	5.3	8.1
CL537-0593-0-51	30	9.7	7.0	7.8	8.2	7.8	10.6
CL537-0594-0-51	32	10.2	7.5	8.3	8.7	8.3	11.1
CL537-0595-0-51	36	11.2	8.5	9.3	9.7	9.3	12.1
CL537-0596-0-51	40	12.2	9.5	10.3	10.7	10.3	13.1
CL537-0597-0-51	50	14.7	12.0	12.8	13.2	12.8	15.6
CL537-0598-0-51	60	17.2	14.5	15.3	15.7	15.3	18.1



NOTES 1 LEAD CO-PLANARITY SHALL BE 0.08 mm MAX.
 2 IF THERE IS PATTERN ON  PART, THERE IS A POSSIBILITY
 THAT IT WILL MAKE CONTACT WITH THE LEADS.
 3 REINFORCED METAL FITTINGS AS FOLLOWS.



			7	PS	CLEAR (REINFORCEMENT COLLAR)
			6	PS	BLACK (PLASTIC REEL)
2	PHOSPHOR BRONZE	CONTACT AREA:GOLD PLATED 0.2#m min	5	POLYESTER	CLEAR (COVER TAPE)
		LEAD AREA:GOLD PLATED 0.015#m min	4	PS	CLEAR (EMBOSSD CARRIER TAPE)
		OTHERS(UNDER PLATING):NICKEL PLATED 2#m min	3	BRASS	TIN PLATED 2#m min (UNDER PLATING):NICKEL 1#m min
1	POLYAMIDE	UL94V-0. BLACK			
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE 5 : 1		COUNT 0	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE

HIROSE ELECTRIC CO., LTD.	APPROVED :WR. FUKUCHI	20191031	DRAWING NO. EDC-390685-51-77 PART NO. DF12NBC(4.0)-*DP-0.5V<51 CODE NO. CL537
	CHECKED :TS. MIYAZAKI	20191031	
	DESIGNED :KT. KUSAKA	20191031	
	DRAWN :KT. KUSAKA	20191030	

