

APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	-30 °C TO +85 °C(NOTE1)		STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C(NOTE2)		
	VOLTAGE	250 V AC		APPLICABLE CONNECTORS	DF1- * P-2.5DS,DF1- * P-2.5DSA		
	CURRENT	AWG24	3A	OPERATING HUMIDITY RANGE	UL1007,AWG24		
SPECIFICATIONS							
ITEM		TEST METHOD		REQUIREMENTS	QT	AT	
CONSTRUCTION							
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.				X	X
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).		30 mΩ MAX.	X	—	
INSULATION RESISTANCE		500 V DC.		1000 MΩ MIN.	X	—	
VOLTAGE PROOF		650 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X	—	
MECHANICAL CHARACTERISTICS							
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			X	—	
ENVIRONMENTAL CHARACTERISTICS							
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→5 TO 35→85→5 TO 35°C TIME 30→ 10 → 30→ 10 min UNDER 5 CYCLES.		① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE:1000 MΩMIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 TO 95 %, 96 h.		① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 1000 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE		
△							
REMARKS				APPROVED	TY. OMA	05.08.11	
NOTE1:INCLUDING THE TEMPERATURE RISING BY CURRENT.				CHECKED	HK. UMEHARA	05.08.11	
Unless otherwise specified, refer to MIL-STD-1344.				DESIGNED	IO. DENPOUYA	05.08.11	
				DRAWN	MK. MATSUO	05.08.08	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-162345-01		
HRS	SPECIFICATION SHEET		PART NO.	DF1-*S-2. 5R24 (05)			
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL543	△	1/	