




APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-30 °C TO +85 °C(NOTE1)	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C	
	OPERATING HUMIDITY RANGE	UL1007, AWG26,28			
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.		X	X
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
					
REMARKS NOTE1:INCLUDING THE TEMPERATURE RISING BY CURRENT. Unless otherwise specified, refer to JIS C 5402.			APPROVED	TY.OMA	05.12.28
			CHECKED	HK.UMEHARA	05.12.28
			DESIGNED	NS.HIROSE	05.12.27
			DRAWN	AK.MIURA	05.12.27
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-162340-01
	SPECIFICATION SHEET		PART NO.	DF1-*A1. 05	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL541	 1/1