


Crimp Contact : Crimp Quality Standard

Part No.	DF1B-****SC(F)(A)(##)	Code No.	CL541-****-**-**
----------	-----------------------	----------	------------------



Check point		Measure (mm)	Remarks
Cover location.	A	0.1 to 0.9	
Location of tip of the core.	B	0.1 to 1.2	
Bell-mouth.	C	0.2 to 0.4	
Bent-up.	D	3° MAX	For the use of applicator, 2° MAX
Bent-down.	E	3° MAX	
Twist.	F	± 3° MAX	
Rolling.	G	± 5° MAX	
Height of Lance	H	0.4 to 0.6	
cut-off tab.	I1	0.1 MAX	
	I2	0.3 MAX	
Strip length.	J	2.0 to 2.5	
Height of metal cut-out teeth.	K	0.1 MAX	

Note 1 To adjust applicator, please check the crimp condition (crimp height and configuration) by using cable.

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
△0					
TITLE DF1B-****SC(F)(A)(##) Crimp Quality Standard			HRS HIROSE ELECTRIC CO., LTD.		
			APPROVED	HS. OKAWA	18.08.31
			CHECKED	SZ. ONO	18.08.31
			CHARGED	TS. KUMAZAWA	18.08.31
			WRITTEN	SN. MIWA	18.08.31
TECHNICAL SPECIFICATION			ETAD-H0909-00	△0	1/1