








Panel thickness	A
0.5~0.8	33.6
0.9~1.3	34.1
1.4~1.8	34.5
1.9~2.3	34.9



- Note 1 Please use non-radius side for the panel hooking area.
2 Applicable panel thicknessing is 2.3 to 0.5 mm.
3 Consult hirose for the other panel cutout designs than recommended one.
4. Per pack : 100 pieces.
5. UL(File No.E52653).
C-UL(File No.E52653) authorization article



NO.				1				PBT				UL94V-0. BLACK			
MATERIAL				FINISH . REMARKS				MATERIAL				FINISH . REMARKS			
UNITS		SCALE		COUNT		DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE			
mm		2 : 1		1		DIS-H-00004547		TS.MIYAKI		SZ.ONO		20181225			
HRS HIROSE ELECTRIC CO., LTD.		APPROVED : HS. OKAWA		20160601		DRAWING NO.		EDC-366292-00-00							
		CHECKED : YN. TAKASHITA		20160601		PART NO.		DF51-24DEP-2C							
		DESIGNED : TT. OHSAKO		20160601		CODE NO.		CL543-5081-0-00							
		DRAWN : TT. OHSAKO		20160601											