

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35 °C TO +85 °C(NOTE 1)	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C(NOTE 3)	
	OPERATING HUMIDITY RANGE	40% TO + 80%(NOTE 2)	STORAGE HUMIDITY RANGE	40% TO + 70%(NOTE 3)	
	VOLTAGE	250V AC/DC	CURRENT	0.5A/pin	
	APPLICABLE CABLE	UL1007,UL1061 : AWG 30			
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100 mA (DC OR 1000 HZ)	30 mΩ MAX.	X	—
INSULATION RESISTANCE		500 V DC.	1000 MΩ MIN.	X	—
VOLTAGE PROOF		650 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE : 30 mΩ MAX ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 TO 95 %, 96 h.	① CONTACT RESISTANCE : 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→ 5 TO 35→85→ 5 TO 35°C TIME 30→ 10 → 30→ 10 min UNDER 5 CYCLES.	① CONTACT RESISTANCE : 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
REMARKS					
NOTE 1:INCLUDING THE TEMPERATURE RISING BY CURRENT. NOTE 2:NO CONDENSING. NOTE 3:APPLY TO UNUSED PRODUCT ON PACKAGED CONDITION.					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
Unless otherwise specified, refer to IEC 60512.			APPROVED	SJ. OKAMURA	20210812
			CHECKED	SZ. ONO	20210812
			DESIGNED	KT. NUMATA	20210812
			DRAWN	NK. OOSHIMA	20210806
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-081078-00-00
HRS	SPECIFICATION SHEET		PART NO.	DF1B-30PCFB	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0541-0688-5-00	△ 1/1