


Applicable standard							
Rating	Operating Temperature range		-35 °C TO +105°C (NOTE1)		Storage Temperature range	-10 °C TO +60°C (NOTE3)	
	Operating Humidity range		20% TO 80% (NOTE2)		Storage Humidity range	40% TO 70% (NOTE3)	
	Applicable Connector		DF62B-13EP-2.2C(##)		Voltage	AC/DC 250V	
	UL・C-UL Rating 	Voltage	250 V AC/DC		Current	AWG 22 : 3A/pin AWG 24 : 2A/pin AWG 26-30 : 1A/pin	
		Current	AWG 22 : 3A/pin AWG 24 : 2A/pin AWG 26-30 : 1A/pin				
	Operating Temperature range	-35 °C TO +75°C (NOTE1)		Applicable contact	DF62-22SC* DF62-2428SC* DF62-30SC*		
Specifications							
Item		Test method		Requirements		QT	AT
Construction							
General examination		Visually and by measuring instrument.		According to drawing.		X	X
Marking		Confirmed visually.				X	X
Electric characteristics							
Insulation resistance		500 V DC.		1000 MΩ MIN.		X	—
Voltage proof		650 V AC for 1 min.		No flashover or breakdown.		X	—
Mechanical characteristics							
Mechanical operation		30 times insertion and extraction.		No damage, crack or looseness of parts.		X	—
Vibration		Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 10 cycles for 3 direction.		No damage, crack or looseness of parts.		X	—
Shock		490 m/s ² duration of pulse 11 ms at 3 times each for 3 both axial directions.		No damage, crack or looseness of parts.		X	—
Environmental characteristics							
Damp heat (Steady state)		Exposed at 40 ± 2°C , 90 to 95 % , 96 h. (After leaving the room temperature for 1—2h.)		①Insulation resistance: 1000 MΩ MIN. ②No damage, crack or looseness of parts.		X	—
Rapid change of temperature		Temperature -55°C→ +85°C Time 30min→ 30min Under 5 cycles. (The transferring time of the tank is 2—3 min) (After leaving the room temperature for 1—2h.)		①Insulation resistance: 1000 MΩ MIN. ②No damage, crack or looseness of parts.		X	—
Note 1: Include the temperature rising by current. Note 2: No condensing Note 3: Apply to the condition of long term storage for unused products before inserting terminal. After inserting terminal, operating temperature and humidity range is applied for interim storage during transportation.							
	Count	Description of revisions	Designed	Checked	Date		
	1	DIS-H-00019419	RI. GENDA	SZ. ONO	20231115		
Remarks Unless otherwise specified, refer to IEC 60512.				Approved	KI. AKIYAMA	20140606	
				Checked	TS. FUKUSHIMA	20140606	
				Designed	TS. KUMAZAWA	20140606	
				Drawn	TS. KUMAZAWA	20140606	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			Drawing No.		ELC-351976-18-02		
	Specification sheet		Part No.	DF62C-13S-2. 2C (18)			
	HIROSE ELECTRIC CO., LTD.		Code No.	CL0544-0571-7-18		1/1	