






Applicable standard							
Rating	Operating Temperature range	-40 °C to +105°C (Note1)		Storage Temperature range	-10 °C to +60°C (Note3)		
	Operating Humidity range	20% to 80%(Note2)		Storage Humidity range	40% to 70% (Note3)		
	Applicable connector	1) DF62W-*EP-2.2C(##) 2) DF62WC-*EP-2.2C(##)		Voltage	250V AC/DC		
	Applicable cable	Applicable connector		Current 	AWG 22 : 4A/pin AWG 24 : 3.5A/pin AWG 26 : 3A/pin		
		1)	UL1007 AWG#22 to 24 UL1430 AWG#24 to 26				
		2)	UL1061 AWG#24 to 26				
Applicable Insulation diameter	Applicable connector						
	1)	φ 1.4 to 1.6mm					
	2)	φ 0.98 to 1.2mm					
Specifications							
Item		Test method		Requirements		QT	AT
Construction							
General examination		Visually and by measuring instrument.		According to drawing.		X	X
Marking		Confirmed visually.				X	X
Electric characteristics							
Contact resistance		20mV MAX, 1mA (DC or 1000Hz).		30 mΩ MAX.		X	—
Mechanical characteristics							
Mechanical operation		50 times insertion and extraction.		1)Contact resistance: 30 mΩ MAX. 2)No damage, crack or looseness of parts.		X	—
Vibration		Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 10 cycles for 3 direction.		1)No electrical discontinuity of 1 μ s. 2)No damage, crack or looseness of parts.		X	—
Shock		490 m/s ² duration of pulse 11 ms at 3 times each for 3 both axial directions.		1)No electrical discontinuity of 1 μ s. 2)No damage, crack or looseness of parts.		X	—
Environmental characteristics							
Damp heat (Steady state)		Exposed at 40 ± 2°C , 90 to 95 %, 96 h. (After leaving the room temperature for 1-2h.)		1)Contact resistance: 30 mΩ MAX. 2)No damage, crack or looseness of parts.		X	—
Rapid change of temperature		Temperature -55°C→ +85°C Time 30min→ 30min Under 5 cycles. (The transferring time of the tank is 2-3 min) (After leaving the room temperature for 1-2h.)		1)Contact resistance: 30 mΩ MAX. 2)No damage, crack or looseness of parts.		X	—
Remarks Note 1: Include the temperature rising by current. Note 2: No condensing. Note 3: Apply to the packaged and unused product. 							
	Count	Description of revisions	Designed	Checked	Date		
	2	DIS-H-00015722	HT. SATO	SZ. ONO	20221017		
Unless otherwise specified, refer to IEC 60512.				Approved	KI. AKIYAMA	20151214	
				Checked	TS. FUKUSHIMA	20151214	
				Designed	YK. YAMAGUCHI	20151211	
				Drawn	MI. SAKIMURA	20151211	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			Drawing No.	ELC-364716-00-00			
	Specification sheet		Part No.	DF62W-EP2226PCFA			
	HIROSE ELECTRIC CO., LTD.		Code No.	CL0544-1026-0-00			1/1