



APPLICABLE STANDARD		UL:UL1977				
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾		STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾	
	VOLTAGE	300 V AC		OPERATING HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX (NOT DEWED)	
	CURRENT	3 A		STORAGE HUMIDITY RANGE		
UL RATING	VOLTAGE	250 V AC				
	CURRENT	1 A				
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT AT	
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	x x	
MARKING		CONFIRMED VISUALLY.			x x	
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).		15 mΩ MAX.	x —	
INSULATION RESISTANCE		500 V DC		1000 MΩ MIN.	x —	
VOLTAGE PROOF		1000 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	x —	
MECHANICAL CHARACTERISTICS						
CONTACT INSERTION AND EXTRACTION FORCES		□0.635±0.002mm BY STEEL GAUGE.		INSERTION FORCE: 4.4 N MAX. EXTRACTION FORCE: 0.56 N MIN.	x —	
MECHANICAL OPERATION		500 TIMES INSERTIONS AND EXTRACTIONS.		①CONTACT RESISTANCE: 15 mΩ MAX. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x —	
VIBRATION		FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, AT 2 h FOR 3 DIRECTIONS.		①NO ELECTRICAL DISCONTINUITY OF 1 μs. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x —	
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			x —	
ENVIRONMENTAL CHARACTERISTICS						
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.		①CONTACT RESISTANCE: 15 mΩ MAX. ②INSULATION RESISTANCE: 1000 MΩ MIN.	x —	
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→+15~+35→+125→+15~+35°C TIME 30 → 10~15 → 30 → 10~15 min. UNDER 5 CYCLES.		③NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x —	
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		①CONTACT RESISTANCE: 15 mΩ MAX. ②NO HEAVY CORROSION.	x —	
SULPHUR DIOXIDE		EXPOSED IN 3 PPM FOR 96 h. (TEST STANDARD: JEIDA - 38)			x —	
RESISTANCE TO SOLDERING HEAT		1) SOLDER BATH: SOLDER TEMPERATURE, 260±5°C FOR IMMERSION, DURATION, 10±1s. 2) SOLDERING IRONS : 360°C FOR 5 s MAX.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	x — x —	
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 245±3°C, FOR IMMERSION DURATION, 2 s.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	x —	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
	2	DIS-F-00005942	AK. IWAHORI	HT. YAMAGUCHI	20200313	
REMARK ⁽¹⁾ TEMPERATURE RISE INCLUDED WHEN ENERGIZED. ⁽²⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED. Unless otherwise specified, refer to MIL-STD-202.				APPROVED	HT. YAMAGUCHI	20181210
				CHECKED	HT. YAMAGUCHI	20181210
				DESIGNED	HR. NAGAYASU	20181207
				DRAWN	TS. HORI	20181207
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC-386223-00-00		
	SPECIFICATION SHEET		PART NO.	HIF3H-*SA-2. 54DSA (61)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.		1/1	