


Part No.	Code No.	A	B	C	D
DF3EA- 2P-2V(51)	CL543-0315-0-51	4.6	2.0	8.5	8.74
DF3EA- 3P-2V(51)	CL543-0316-0-51	6.6	4.0	10.5	10.74
DF3EA- 4P-2V(51)	CL543-0317-0-51	8.6	6.0	12.5	12.74
DF3EA- 5P-2V(51)	CL543-0318-0-51	10.6	8.0	14.5	14.74
DF3EA- 6P-2V(51)	CL543-0319-0-51	12.6	10.0	16.5	16.74
DF3EA- 7P-2V(51)	CL543-0320-0-51	14.6	12.0	18.5	18.74
DF3EA- 8P-2V(51)	CL543-0321-0-51	16.6	14.0	20.5	20.74
DF3EA- 9P-2V(51)	CL543-0322-0-51	18.6	16.0	22.5	22.74
DF3EA-10P-2V(51)	CL543-0323-0-51	20.6	18.0	24.5	24.74
DF3EA-11P-2V(51)	CL543-0324-0-51	22.6	20.0	26.5	26.74
DF3EA-12P-2V(51)	CL543-0325-0-51	24.6	22.0	28.5	28.74
DF3EA-13P-2V(51)	CL543-0326-0-51	26.6	24.0	30.5	30.74
DF3EA-14P-2V(51)	CL543-0327-0-51	28.6	26.0	32.5	32.74
DF3EA-15P-2V(51)	CL543-0328-0-51	30.6	28.0	34.5	34.74

2	Brass	Surface:Gold plated 0.2μm MIN Under plating:Nickel plated 1μm MIN	5	Polyester	Clear(Cover tape)
1	Polyamide	Natural(Beige), UL94V-0	4	PS	Clear(Embossed carrier tape)
			3	Brass	Surface:Tin plated 1μm MIN (Under plating)Nickel plated 1μm MIN
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 5 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED SN. MIWA
			3	DIS-H-00006609	CHECKED SZ. ONO
					DATE 20201105
 HIROSE ELECTRIC CO., LTD.	APPROVED : KI. AKIYAMA	20160208	DRAWING NO.	EDC-367142-51-00	
	CHECKED : TS. FUKUSHIMA	20160205	PART NO.	DF3EA- * P-2V(51)	
	DESIGNED : HT. SATO	20160205	CODE NO.	CL543-	
	DRAWN : MI. SAKIMURA	20160205			



Part No.	Code No.	Number of contact	E	F	G	H
DF3EA- 2P-2V(51)	CL543-0315-0-51	2	24.0		11.5	24.4
DF3EA- 3P-2V(51)	CL543-0316-0-51	3	24.0		11.5	24.4
DF3EA- 4P-2V(51)	CL543-0317-0-51	4	24.0		11.5	24.4
DF3EA- 5P-2V(51)	CL543-0318-0-51	5	32.0	28.4	14.2	32.4
DF3EA- 6P-2V(51)	CL543-0319-0-51	6	32.0	28.4	14.2	32.4
DF3EA- 7P-2V(51)	CL543-0320-0-51	7	32.0	28.4	14.2	32.4
DF3EA- 8P-2V(51)	CL543-0321-0-51	8	44.0	40.4	20.2	44.4
DF3EA- 9P-2V(51)	CL543-0322-0-51	9	44.0	40.4	20.2	44.4
DF3EA-10P-2V(51)	CL543-0323-0-51	10	44.0	40.4	20.2	44.4
DF3EA-11P-2V(51)	CL543-0324-0-51	11	56.0	52.4	26.2	56.4
DF3EA-12P-2V(51)	CL543-0325-0-51	12	56.0	52.4	26.2	56.4
DF3EA-13P-2V(51)	CL543-0326-0-51	13	56.0	52.4	26.2	56.4
DF3EA-14P-2V(51)	CL543-0327-0-51	14	56.0	52.4	26.2	56.4
DF3EA-15P-2V(51)	CL543-0328-0-51	15	56.0	52.4	26.2	56.4

Notes

- 1 reel 1000 connectors.
- At the beginning of the reel, 30 boxes shall be empty.
At The end of the reel, 20 boxes shall be empty.
- When the tape width is 32, 44 and 56 mm, sprocket holes shall be set on both sides of reel as shown on this drawing.

	DRAWING NO.	EDC-367142-51-00		
	PART NO.	DF3EA-*P-2V(51)		
	CODE NO.	CL543-		2 2