

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +85 °C (NOTE1) 	STORAGE TEMPERATURE RANGE	-10°C TO +60 °C (NOTE2)	
	OPERATING HUMIDITY RANGE	40% TO + 80%	STORAGE HUMIDITY RANGE	40% TO + 70% (NOTE2)	
	VOLTAGE	100 V AC	APPLICABLE CABLE	UL1061 AWG26	
	CURRENT	1 A			
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X X
MARKING		CONFIRMED VISUALLY.			X X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).		30 mΩ MAX.	X -
INSULATION RESISTANCE		500 V DC.		1000 MΩ MIN.	X -
VOLTAGE PROOF		650 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X -
MECHANICAL CHARACTERISTICS					
CONTACT INSERTION AND EXTRACTION FORCES		□0.5±0.002mm BY STEEL GAUGE.		INSERTION FORCE: 4.4 N MAX. EXTRACTION FORCE: 0.3 N MIN.	X -
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X -
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 10μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X -
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			X -
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.		① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X -
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55±3→5TO35→+85±2→5TO35 °C TIME 30 → 5 → 30 → 5 min UNDER 5 CYCLES.		① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X -
REMARKS					
NOTE1: INCLUDING THE TEMPERATURE RISE BY CURRENT.					
NOTE2: APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD, AFTER PCB BOARD, OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION.					
Unless otherwise specified, refer to IEC 60512.					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	1	DIS-H-008540	MI. SAKIMURA	HK. UMEHARA	14. 02. 26
			APPROVED	TY. OMA	06. 03. 13
			CHECKED	HK. UMEHARA	06. 03. 10
			DESIGNED	NS. HIROSE	06. 03. 08
			DRAWN	AK. MIURA	06. 02. 22
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-071615-01
	SPECIFICATION SHEET		PART NO.	DF11-*DS-2R26 (05)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL543	 1/1