

APPLICABLE STANDARD								
Rating	Operating Temperature Range	-55 °C to 85 °C ⁽¹⁾		Storage Temperature Range	-10 °C to 60 °C ⁽²⁾			
	Voltage	50 V AC		Storage Humidity Range	Relative humidity 85% max (Not dewed)			
	Current	0.5 A		Operating Humidity Range				
SPECIFICATIONS								
ITEM		TEST METHOD		REQUIREMENTS		QT	AT	
CONSTRUCTION								
General Examination		Visually and by measuring instrument.		According to drawing.		×	×	
Marking		Confirmed visually.				×	×	
ELECTRIC CHARACTERISTICS								
Contact Resistance		100 mA(DC or 1000Hz)		70 mΩ MAX.		×	—	
Insulation Resistance		100 V DC.		100 MΩ MIN.		×	—	
Voltage Proof		150 V AC for 1 min.		No flashover or breakdown.		×	×	
MECHANICAL CHARACTERISTICS								
Insertion And Withdrawal Forces		Measured by applicable connector.		Insertion Force: 14 N MAX. Withdrawal Force: 1.8 N MIN.		×	—	
Mechanical Operation		50 times insertions and extractions.		① Contact Resistance: Variation from initial value 20 mΩ or less. ② No damage, crack and looseness of parts.		×	—	
Vibration		Frequency 10 to 55 to 10Hz, approx 5min Single Amplitude : 0.75 mm, 10 cycles for 3 axial directions.		① No electrical discontinuity of 1 μs. ② No damage, crack and looseness of parts.		×	—	
Shock		490 m/s ² , duration of pulse 11 ms at 3 times for 3 both axial directions.				×	—	
ENVIRONMENTAL CHARACTERISTICS								
Damp Heat (Steady state)		Exposed at 40±2 °C, 90 ~ 95 %, 96 h.		① Contact Resistance: Variation from initial value 20 mΩ or less.		×	—	
Rapid Change of Temperature		Temperature -55 → +85 °C Time 30 → 30 min. Under 5 cycles. (Relocation time to chamber:within 2~3 MIN)		② Insulation Resistance : 100 MΩ MIN. ③ No damage, crack and looseness of parts.		×	—	
Cold		Exposed at -55°C, 96 h		① Contact Resistance: Variation from initial value 20 mΩ or less.		×	—	
Dry Heat		Exposed at 85°C, 96 h		② No damage, crack and looseness of parts.		×	—	
Sulfur Dioxide		Exposed at 25±2°C, 75±5%RH, 25 PPM for 96 h. (Test standard : JIS C 60068)		① No defect such as corrosion which impairs the function of connector. ② Contact Resistance: variation from initial value 20 mΩ or less.		×	—	
Resistance to Soldering Heat		1)Reflow Soldering : Peak TMP : 260°C MAX Reflow TMP: 220°C MIN for 60sec 2) Soldering Irons : 360°C MAX. for 5 sec.		No deformation of case of excessive looseness of the terminal.		×	—	
Solderability		Soldered at solder temperature 240±3°C for immersion duration, 3 sec.		A new uniform coating of solder shall cover a minimum of 95 % of the surface being immersed.		×	—	
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE
△								
REMARKS ⁽¹⁾ Include temperature rise caused by current-carrying. ⁽²⁾ "STORAGE" means a long-term storage state for the unpacked part before assembly to PCB.				APPROVED	HS. OKAWA	14. 05. 29		
				CHECKED	KN. SHIBUYA	14. 05. 29		
				DESIGNED	TS. OONO	14. 05. 29		
				DRAWN	TS. OONO	14. 05. 29		
Unless otherwise specified, refer to JIS-C-5402.								
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC4-350411-00		
HRS	SPECIFICATION SHEET			PART NO.		FX20-20S-0. 5SH		
	HIROSE ELECTRIC CO., LTD.			CODE NO.		CL570-1611-1-00		△ 1/1