





COUNT		DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
	△				• •	△				• •
	△				• •	△				• •
	△				• •	△				• •



AA(10:1)



RECOMMENDED LAND PATTERN DIMENSION OF P.C.B.



NOTE

- 1 LEAD-COPLANARITY OF THIS PRODUCT TO BE 0.1MAX FOR SMT LEAD AND 0.15MAX FOR GROUND PLATE LEAD
- 2 DO NOT MOUNT OTHER DEVICES ONTO  AREA, OR MATINGPAIR CANNOT BE MATED AND OPERATED THE LOCK PARTS.
- 3  AREA OF INNER SMT LAND REQUIRES PATTERN PROHIBITION OR RESIST TREATMENT TO PREVENT THE PATTERN TOUCHING TO THE CONTACTS.
- 4  AREA IS VACUUM PICKUP AREA FOR REFERENCE.
- 5 THE DIMENSION IS THE CENTER OF VACUUM PICKUP AREA.
- 6 THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
- 7 PACKAGING FOR THIS PRODUCT APPLIES EMBOSSED CARRIER TAPE PACKAGING. SEE SHEET 2/2 FOR DETAILS.

3	NICKEL SILVER		2	PHOSPHOR BRONZE	CONTACT AREA: GOLD 0.1 μ m min
1	PA	BLACK			LEAD AREA: TIN-PLATING 1 μ m min
NO.	MATERIAL	UL94V-O			UNDER PLATING: NICKEL 0.5 μ m min
			NO.	MATERIAL	FINISH. REMARKS

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
CL	K. SHIBUYA	K. Shibuya	H. Yamaguchi	H. Kanwa	
	05.08.04	05.08.04	05.08.05	05.08.05	

	DRAWING NO.		PART NO.	FX15S-41S-0.5SH
SCALE 4 : 1	EDC3-155937			
UNITS mm	 HIROSE ELECTRIC CO., LTD		CODE NO.	CL575-2307-8
1/2				

1	2	3	4	5	6	7	8
---	---	---	---	---	---	---	---

FORM NO. 229 (H)