

APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE		-55 °C TO 85 °C ⁽¹⁾	STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾		
	VOLTAGE		100 V AC	OPERATING HUMIDITY RANGE	40 % TO 80 %		
	CURRENT		0.5 A	STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾		
SPECIFICATIONS							
ITEM		TEST METHOD		REQUIREMENTS		QT	AT
CONSTRUCTION							
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		×	×
MARKING		CONFIRMED VISUALLY.				×	×
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).		40 mΩ MAX .		×	-
CONTACT RESISTANCE		20 mV MAX, 1 mA(DC OR 1000Hz)		50 mΩ MAX .		×	-
MILLIVOLT LEVEL METHOD							
INSULATION RESISTANCE		250 V DC		100 MΩ MIN.		×	-
VOLTAGE PROOF		300 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		×	-
MECHANICAL CHARACTERISTICS							
MECHANICAL OPERATION		100 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	-
VIBRATION		FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, AT 2 h FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	-
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.				×	-
ENVIRONMENTAL CHARACTERISTICS							
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN.		×	-
RAPID CHANGE OF TEMPERATURE		TEMPERATURE-55→+15~+35→ +85→+15~+35°C TIME 30 → MAX 5 → 30 → MAX 5 min UNDER 5 CYCLES.		③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	-
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO HEAVY CORROSION.		×	-
HYDROGEN SULPHIDE		EXPOSED IN 3 PPM FOR 96 h. (TEST STANDARD: JEIDA 38)				×	-
RESISTANCE TO SOLDERING HEAT		1) REFLOW SOLDERING : 250 °C MAX, : 220 °C MIN, FOR 60 s 2) SOLDERING IRONS : 360 °C, FOR 5 s		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.		×	-
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 240±3°C, FOR IMMERSION DURATION, 3 s.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.		×	-
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED	DATE
△0							
REMARK ⁽¹⁾ TEMPERATURE RISE INCLUDED WHEN ENERGIZED. ⁽²⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.				APPROVED	HS.OKAWA	06.05.24	
				CHECKED	HS.OZAWA	06.05.24	
				DESIGNED	KY.NAKAMURA	06.05.24	
Unless otherwise specified, refer to MIL-STD-1344.				DRAWN	AK.SUZUKAWA	06.05.23	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC4-071174-25	
		SPECIFICATION SHEET		PART NO.		FX6-*P-0.8SV(71)	
		HIROSE ELECTRIC CO., LTD.		CODE NO.		CL576	
						△0	1/1