


May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



NOTE1 RECOMMEND PC BOARD HOLE DIAMETER $\phi 1 \begin{smallmatrix} +0.1 \\ 0 \end{smallmatrix}$
2 UL (FILE NO. E52653)



CODE NO.	PART NO.	NUMBER OF CONTACTS	A	B
CL547-0304-0-95	MDF7B- 3P-2.54DSA(95)	3	7.62	5.08
CL547-0133-9-95	MDF7B- 5P-2.54DSA(95)	5	12.70	10.16
CL547-0131-3-95	MDF7B- 6P-2.54DSA(95)	6	15.24	12.70
CL547-0177-4-95	MDF7B- 7P-2.54DSA(95)	7	17.78	15.24
CL547-0178-7-95	MDF7B- 8P-2.54DSA(95)	8	20.32	17.78
CL547-0179-0-95	MDF7B- 9P-2.54DSA(95)	9	22.86	20.32
CL547-0048-1-95	MDF7B-10P-2.54DSA(95)	10	25.40	22.86
CL547-0047-9-95	MDF7B-11P-2.54DSA(95)	11	27.94	25.40
CL547-0041-2-95	MDF7B-12P-2.54DSA(95)	12	30.48	27.94
CL547-0180-9-95	MDF7B-13P-2.54DSA(95)	13	33.02	30.48
CL547-0181-1-95	MDF7B-14P-2.54DSA(95)	14	35.56	33.02
CL547-0024-3-95	MDF7B-15P-2.54DSA(95)	15	38.10	35.56
CL547-0182-4-95	MDF7B-16P-2.54DSA(95)	16	40.64	38.10
CL547-0183-7-95	MDF7B-17P-2.54DSA(95)	17	43.18	40.64
CL547-0025-6-95	MDF7B-18P-2.54DSA(95)	18	45.72	43.18
CL547-0184-0-95	MDF7B-19P-2.54DSA(95)	19	48.26	45.72
CL547-0052-9-95	MDF7B-20P-2.54DSA(95)	20	50.80	48.26
CL547-0185-2-95	MDF7B-21P-2.54DSA(95)	21	53.34	50.80
CL547-0186-5-95	MDF7B-22P-2.54DSA(95)	22	55.88	53.34
CL547-0066-3-95	MDF7B-23P-2.54DSA(95)	23	58.42	55.88
CL547-0067-6-95	MDF7B-24P-2.54DSA(95)	24	60.96	58.42
CL547-0026-9-95	MDF7B-25P-2.54DSA(95)	25	63.50	60.96

1	BRASS	SURFACE: TIN PLATED 1μm		2	PBT	UL94V-0, BLACK		
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS		
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
HIROSE ELECTRIC CO., LTD.		APPROVED : WR. FUKUCHI	18.05.25	DRAWING NO.		EDC-162732-95-01		
		CHECKED : TS. MIYAZAKI	18.05.24	PART NO.		MDF7B-P-2.54DSA(95)		
		DESIGNED : KT. KUSAKA	18.05.24	CODE NO.		CL547		
		DRAWN : KT. KUSAKA	18.05.22					