







APPLICABLE STANDARD					
Rating	Operating Temperature Range	-40 °C to 140 °C ⁽¹⁾	Storage Temperature Range	-10 °C to 60 °C ⁽²⁾	
	Voltage	125 V AC ⁽³⁾	Storage Humidity Range	Relative humidity 60% max (Not dewed)	
	Current	0.5 A	Operating Humidity Range	Relative humidity 85% max (Not dewed)	
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	
CONSTRUCTION				QT	AT
General Examination		Examined visually and with a measuring instrument.		According to the drawing.	× ×
Marking		Confirmed visually.			
ELECTRICAL CHARACTERISTICS					
Contact Resistance		Measured at 100 mA MAX.(DC or 1000Hz)		65m Ω MAX.	× —
Insulation Resistance		Measured at 250 V DC.		1000 MΩ MIN.	× —
Voltage Proof		375 V AC applied for 1 min.		No flashover or breakdown.	× —
MECHANICAL CHARACTERISTICS					
Mating and Unmating Forces		Measured with an applicable connector.		Mating Force: 30 N MAX. Unmating Force: 3.3 N MIN.	× —
Mechanical Operation		Mated and unmated 10 times.		①Contact Resistance : 75m Ω MAX. ②No damage, cracks or looseness of parts.	× —
Vibration		Frequency 50~100 → 100~150 → 150~300Hz Acceleration 98 → 98~294 → 294 m/s ² 1 cycle 3 min 3 h for 3 axial directions ⁽⁴⁾		①No electrical discontinuity of more than 1 μs. ②No damage, cracks or looseness of parts.	× —
Shock		Acceleration 980 m/s ² , duration of pulse 6 ms at 3 times for 3 axial directions.			
ENVIRONMENTAL CHARACTERISTICS					
Damp Heat (Steady state)		Exposed at 60±2 °C, 90 ~ 95 %, 1000 h.		①Contact Resistance : 75m Ω MAX. ②Insulation Resistance : 1000 MΩ MIN.  ③No damage, cracks or looseness of parts.	× —
Rapid Change of Temperature		Temperature -40 → +140 °C Time 30 → 30 min. under 1000 cycles. (Relocation time to chamber : within 2~3 MIN)			
Cold		Exposed at -40°C, 1000 h		①Contact Resistance : 75m Ω MAX. ②No damage, cracks or looseness of parts.	× —
Dry Heat		Exposed at 140°C, 1000 h			
Sulfur Dioxide		Exposed at 40±2°C, 80±5%RH, 25±5ppm  for 96 h.		Contact Resistance : 75m Ω MAX.	× —
Resistance to Soldering Heat		1)Reflow soldering : Peak TMP : 260°C MAX Reflow TMP: 220°C MIN for 60sec 		No deformation of case of excessive looseness of the terminal.	× —
Solderability		Soldered at solder temperature 240±3°C for immersion duration, 3 sec.		A new uniform coating of solder shall cover a minimum of 95 % of the surface being immersed.	× —
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	1	DIS-F-00016361	TK. ABE	HH. SHINDO	20221215
Notes ⁽¹⁾ Include temperature rise caused by current-carrying. ⁽²⁾ “STORAGE” means a long-term storage state for the unused product before assembly to PCB. ⁽³⁾ The creepage distance conforms to IEC 60664-1. Voltage effective value: 32V AC, Pollution Degree: 2 ⁽⁴⁾ Amplitude between connector mounting part and PCB is 0.05mm MAX.			APPROVED	HH. SHINDO	20190809
			CHECKED	KN. SHIBUYA	20190809
			DESIGNED	KT. DOI	20190809
			DRAWN	KI. YAMAZAKI	20190809
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-376642-00-00
	SPECIFICATION SHEET		PART NO.	FX26-30S-1SV15	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0576-1203-0-00	 1/1