

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾	STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾	
	VOLTAGE	50 V AC	OPERATING HUMIDITY RANGE	RELATIVE HUMIDITY 95 % RH MAX. ⁽³⁾	
	CURRENT	0.3 A	STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	x	x
MARKING		CONFIRMED VISUALLY.		x	x
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).	60 mΩ MAX.	x	
INSULATION RESISTANCE		100 V DC	100 MΩ MIN.	x	
VOLTAGE PROOF		150 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	x	x
MECHANICAL CHARACTERISTICS					
INSERTION AND WITHDRAWAL FORCE		MEASURED BY APPLICABLE CONNECTOR.	INSERTION FORCE: 60 N MAX. WITHDRAWAL FORCE: 6.5 N MIN.	x	
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 70 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE : 0.75 mm, AT 10 CYCLES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		x	
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.	① CONTACT RESISTANCE: 70 mΩ MAX. ② INSULATION RESISTANCE: 100 MΩ MIN.	x	
RAPID CHANGE OF TEMPERATURE		TEMPERATURE-55→+15~+35→+85→+15~+35°C TIME 30 → 2 ~ 3 → 30 → 2 ~ 3 min. UNDER 5 CYCLES.	③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	
DRY HEAT		EXPOSED AT 85 °C, 96h.	① CONTACT RESISTANCE: 70 mΩ MAX.	x	
COLD		EXPOSED AT - 55 °C, 96h.	② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	① CONTACT RESISTANCE: 70 mΩ MAX. ② NO HEAVY CORROSION.	x	
SULPHUR DIOXIDE		EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD: JIS C 0090)		x	
RESISTANCE TO SOLDERING HEAT		1) REFLOW SOLDERING : 250 °C MAX, : 220 °C MIN, FOR 60 s 2) SOLDERING IRONS : 360 °C, FOR 5 s	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINAL.	x	
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 240°C, FOR IMMERSION DURATION, 3 s.	A NEW UNIFORM COATING OF SOLDER SHALL OVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	x	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
					
REMARK ⁽¹⁾ TEMPERATURE RISE INCLUDED WHEN ENERGIZED. ⁽²⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED. ⁽³⁾ NO DEW CONDENSATION IS PERMITTED.			APPROVED	HS. OKAWA	10. 08. 16
			CHECKED	HT. YAMAGUCHI	10. 08. 16
			DESIGNED	SY. KAMIGA	10. 08. 07
Unless otherwise specified, refer to JIS C 5402.			DRAWN	HK. SUNADORI	10. 08. 06
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-151949-21
	SPECIFICATION SHEET		PART NO.	FX10B-100P/10-SV (91)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL570-0022-5-91	 1/1