




Drawing for mating
(No scale)

FX20-140S-0.5SV10



Drawing for mating
(No scale)

FX20-140S-0.5SV




2 Drawing for packing(No scale)



Contact No. 1

- 1 Lead CO-Planarity is 0.1mm MAX.
- 2 This is packaged in tray. (50pcs/tray)
- 3 Floating range of this connector is $\pm 0.6\text{mm}$ MAX.
- 4 Blemish and hit mark can be occurred through out the manufacturing process which doesn't affect quality level.
- 5 Please note that excessive wrenching force could damage this connector.
Please refer to the guideline for detailed regulations of the mating method.
- 6 The dimensions in parentheses are for references.

			4	BRASS	TIN-PLATING 1 μm					
2	POLYAMIDE	BLACK UL94V-0	3	COPPER ALLOY	CONTACT AREA:GOLD 0.1 μm					
1	POLYAMIDE	BLACK UL94V-0			LEAD AREA :GOLD 0.03 μm					
					UNDER PLATING:NICKEL 1 μm					
NO.		MATERIAL		FINISH . REMARKS						
UNITS mm				SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED : HS. OKAWA		13. 10. 07		DRAWING NO. EDC3-336324-00				
		CHECKED : KI. HIROKAWA		13. 10. 07		PART NO. FX20-140P-0.5SV15				
		DESIGNED : TS. OONO		13. 10. 07		CODE NO. CL570-1006-4-00				
		DRAWN : TS. OONO		13. 10. 07						
								 		