Sep.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C (1)	STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C (2)
	VOLTAGE	200 V AC	OPERATING HUMIDITY RANGE	40 % TO 80 %
	CURRENT	1 A	STORAGE HUMIDITY RANGE	40 % TO 70 % (2)

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING	CONFIRMED VISUALLY.		×	×
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	100 mA (DC or 1000 Hz).	15 mΩ MAX.	×	—
INSULATION RESISTANCE	500 V DC.	1000 MΩ MIN.	×	—
VOLTAGE PROOF	650 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	×	—
MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	500 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 15 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
VIBRATION	FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, AT 2 h FOR 3 DIRECTION.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
SHOCK	490 m/s², DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		×	—
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 ～ 95 %, 96 h.	① CONTACT RESISTANCE: 15 mΩ MAX. ② INSULATION RESISTANCE:1000 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → +85 °C TIME 30 → 30 min. UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER:WITHIN 2～3 MIN)		×	—
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	① CONTACT RESISTANCE: 15 mΩ MAX. ② NO HEAVY CORROSION.	×	—
HYDROGEN SULPHIDE	EXPOSED IN 3 PPM FOR 120 h.		×	—
RESISTANCE TO SOLDERING HEAT	1) SOLDER BATH:SOLDER TEMPERATURE, 260±5℃ FOR IMMERSION,DURATION,10±1s.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	×	—
	2) SOLDERING IRONS : 360℃ FOR 5 s MAX.		×	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245±3°C, FOR IMMERSION DURATION, 2 s.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	×	—

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△0					

REMARK (1) TEMPERATURE RISE INCLUDED WHEN ENERGIZED.
(2) THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.

Unless otherwise specified, refer to MIL-STD-202.

APPROVED	HS. OKAWA	15. 07. 29
CHECKED	HT. YAMAGUCHI	15. 07. 29
DESIGNED	TH. SANO	15. 07. 28
DRAWN	HR. NAGAYASU	15. 07. 28

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

DRAWING NO. ELC-016898-71-00

HRS	SPECIFICATION SHEET	PART NO.	HIF3E-16PA-2.54DS(71)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL614-0042-2-71	△0 1/1

FORM HD0011-2-1