


Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




PART No.	CODE No.	3	A	B	C	D	E	F	G
HIF6- 20PA-1.27DSA(71)	CL630-0101-9-71	20	30.95	11.43	24.55	18.75	14.95	21.59	43.55
HIF6- 26PA-1.27DSA(71)	CL630-0102-1-71	26	34.76	15.24	28.36	22.56	18.76	25.40	47.36
HIF6- 32PA-1.27DSA(71)	CL630-0103-4-71	32	38.57	19.05	32.17	26.37	22.57	29.21	51.17
HIF6- 34PA-1.27DSA(71)	CL630-0104-7-71	34	39.84	20.32	33.44	27.64	23.84	30.48	52.44
HIF6- 40PA-1.27DSA(71)	CL630-0105-0-71	40	43.65	24.13	37.25	31.45	27.65	34.29	56.25
HIF6- 50PA-1.27DSA(71)	CL630-0106-2-71	50	50.00	30.48	43.60	37.80	34.00	40.64	62.60
HIF6- 52PA-1.27DSA(71)	CL630-0107-5-71	52	51.27	31.75	44.87	39.07	35.27	41.91	63.87
HIF6- 60PA-1.27DSA(71)	CL630-0108-8-71	60	56.35	36.83	49.95	44.15	40.35	46.99	68.95
HIF6- 68PA-1.27DSA(71)	CL630-0109-0-71	68	61.43	41.91	55.03	49.23	45.43	52.07	74.03
HIF6- 80PA-1.27DSA(71)	CL630-0110-0-71	80	69.05	49.53	62.65	56.85	53.05	59.69	81.65
HIF6-100PA-1.27DSA(71)	CL630-0111-2-71	100	81.75	62.23	75.35	69.55	65.75	72.39	94.35


COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE

RECOMMENDED PC BOARD HOLE PATTERN (MOUNT SIDE)

POLARIZING SLOT SIDE



POLARIZING SLOT SIDE



- NOTE 1 THE UPPER DIMENSION SHOWS WHEN THE LOCK OPEN OUT.
2 THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
3 NUMBER OF CONTACTS.

3	STAINLESS STEEL		4, 5	BRASS	CONTACT AREA: GOLD 0.2 μ m min. DIP AREA: TIN-PLATING 2 μ m min. UNDER PLATING: NICKEL 2.5 μ m min.
1, 2	PBT	BLACK UL94V-0			
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD) CL			DRAWN A. SUZUKAWA 06.03.30	DESIGNED H. Nakamura 06.04.04	CHECKED H. Ogawa 06.04.04
			APPROVED H. Okawa 06.04.04	RELEASED	
SCALE FREE	DRAWING NO. EDC3-153148-21		PART NO. HIF6-**-PA-1.27DSA(71)		
UNITS mm	HIROSE ELECTRIC CO., LTD		CODE NO. CL630		1/1