

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO +85 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C		
	VOLTAGE	AC 50 V	OPERATING HUMIDITY RANGE	RELATIVE HUMIDITY: 90% MAX (NO DEW CONDENSATION IS PERMITTED)		
	CURRENT	SIGNAL: 0.2A POWER: REFER TO TEST REPORT TR636E-20282 FOR SPECIFIC POWER APPLICATIONS OR CONTACT HIROSE.				
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUAL AND WITH MEASURING INSTRUMENT		ACCORDING TO A DRAWING	X	X
MARKING		CONFIRM VISUALLY			X	X
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE [EIA-364-23]		100 mA		60 mΩ MAX (*1) MATED WITH IT5**-200S-BGA(**)	X	X
INSULATION RESISTANCE [EIA-364-21]		100 V DC		1000 MΩ MIN	X	—
VOLTAGE PROOF [EIA-364-20]		150 V AC FOR 1 min		NO FLASHOVER OR BREAKDOWN	X	X
MECHANICAL CHARACTERISTICS						
INSERTION AND WITHDRAWAL FORCES [EIA-364-13]		MEASURED WITH RESPECT TO APPLICABLE CONNECTORS		INSERTION FORCE: 90 N MAX WITHDRAWAL FORCE: 10 N MIN	X	—
MECHANICAL OPERATION [EIA-364-09]		100 TIMES INSERTION AND EXTRACTION		1) CONTACT RESISTANCE CHANGE: 20 mΩ OR LESS 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS	X	—
RANDOM VIBRATION [EIA-364-28]		FREQUENCY: 50 TO 2000 Hz POWER SPECTRAL DENSITY: 0.1 G ² /Hz FOR 90 min IN THREE DIRECTIONS		1) NO ELECTRICAL DISCONTINUITY OF 1μs OR MORE 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS	X	—
SHOCK [EIA-364-27]		490 m/s ² , DURATION OF PULSE: 11 ms 18 TIMES TOTAL, 3 EACH DIRECTION, 3 AXIS			X	—
ENVIRONMENTAL CHARACTERISTICS						
THERMAL SHOCK [EIA-364-32]		TEMPERATURE(°C): -55 → 20 ~ 35 → 85 → 20 ~ 35 TIME(min): 30 → 5MAX → 30 → 5MAX UNDER 10 CYCLES		1) CONTACT RESISTANCE CHANGE: 20 mΩ OR LESS 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS	X	—
CYCLIC TEMPERATURE AND HUMIDITY [EIA-364-31]		@ 25 °C, 80% RH: 60 min DWELL TIME ↓ 30 min RAMP TIME @ 65 °C, 50% RH: 60 min DWELL TIME UNDER 24 CYCLES			X	—
DRY HEAT [EIA-364-17]		EXPOSED AT 105 °C, 120 HOURS		1) CONTACT RESISTANCE CHANGE: 20 mΩ OR LESS 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS	X	—
MIXED FLOWING GAS [EIA-364-65]		EXPOSED AT 30 °C, 70% RH Cl ₂ : 10 ppb, NO ₂ : 200 ppb, H ₂ S : 10 ppb, SO ₂ : 100 ppb UNMATED 7 DAYS → MATED 7 DAYS		1) CONTACT RESISTANCE CHANGE: 20 mΩ OR LESS 2) NO HEAVY CORROSION	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
REMARK (*1) THE VALUE OF CONTACT RESISTANCE INCLUDES 2 CONTACT POINTS AND THE BULK RESISTANCE. (*2) REFER TO TEST REPORT TR636E-10259 FOR FULL ELECTRICAL CHARACTERISTICS, MECHANICAL CHARACTERISTICS AND ENVIRONMENTAL CHARACTERISTICS TESTS AND RESULTS.				APPROVED	MK. EZAKI	14. 11. 08
				CHECKED	TS. OSHIDA	14. 11. 08
				DESIGNED	TF. SUGAWARA	14. 11. 08
				DRAWN	TF. SUGAWARA	14. 11. 08
NOTE -- QT: QUALIFICATION TEST; AT: ASSURANCE TEST; X: APPLICATION TEST			DRAWING NO.	ELC4-341075-01		
		SPECIFICATION SHEET		PART NO.	IT5-200P-18H (03)	
		HIROSE ELECTRIC (U.S.A.), INC.		CODE NO.	CL636-1044-0-03	1/1