

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾	STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾	
	VOLTAGE	200 V AC	OPERATING HUMIDITY RANGE	40 % TO 80 %.	
	CURRENT	1 A	STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING		CONFIRMED VISUALLY.		×	×
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).	15 mΩ MAX.	×	—
INSULATION RESISTANCE		500 V DC	1000 MΩ MIN.	×	—
VOLTAGE PROOF		650 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	×	—
MECHANICAL CHARACTERISTICS					
CONTACT INSERTION AND EXTRACTION FORCES		□0.5±0.002mm BY STEEL GAUGE.	INSERTION FORCE: 2.45 N MAX. EXTRACTION FORCE: 0.25 N MIN.	×	—
MECHANICAL OPERATION		100 TIMES INSERTIONS AND EXTRACTIONS.	①CONTACT RESISTANCE: 20 mΩ MAX. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
VIBRATION		FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, 2 h IN 3 DIRECTIONS.	①NO ELECTRICAL DISCONTINUITY OF 1 μs. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms FOR 3 TIMES IN 3 DIRECTIONS.		×	—
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.	①CONTACT RESISTANCE: 20 mΩ MAX. ②INSULATION RESISTANCE:1000 MΩ MIN.	×	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE-65→+15~+35→+125→+15~+35°C TIME 30 → 10~15 → 30 → 10~15 min. UNDER 5 CYCLES.	③NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	①CONTACT RESISTANCE: 20 mΩ MAX. ②NO HEAVY CORROSION.	×	—
SULPHUR DIOXIDE		EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD: JEIDA - 39)		×	—
RESISTANCE TO SOLDERING HEAT		1) SOLDER BATH:SOLDER TEMPERATURE, 260±5°C FOR IMMERSION,DURATION,10±1s. 2) SOLDERING IRONS : 350°C FOR 3 s MAX.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	×	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 245±3°C, FOR IMMERSION DURATION, 2 s.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	×	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARK ⁽¹⁾ TEMPERATURE RISE INCLUDED WHEN ENERGIZED. ⁽²⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.			APPROVED	HS.OKAWA	06.01.05
			CHECKED	HS.OZAWA	05.12.28
			DESIGNED	TK.YANAGISAWA	05.12.26
Unless otherwise specified, refer to MIL-STD-1344.			DRAWN	TK.YANAGISAWA	05.12.26
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-082764-21
HRS	SPECIFICATION SHEET		PART NO.	A3C-50DA-2DSA (71)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL621-0524-1-71	△ 1/1