

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C (NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C	
	VOLTAGE	30V AC	APPLICABLE CONNECTOR	DF36-25P-0.4SD	
	CURRENT	0.25A			
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100m A (DC OR 1000 Hz).	CONTACT:80mΩ MAX. SHIELDING:80mΩ MAX.	X	—
INSULATION RESISTANCE		100V DC.	50MΩ MIN.	X	—
VOLTAGE PROOF		100V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION		30TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: NO VARIATION OF 50 mΩ OR MORE FROM INITIAL VALUE. SHIELDING RESISTANCE: NO VARIATION OF 50 mΩ OR MORE FROM INITIAL VALUE. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, 3 DIRECTIONS × 10 CYCLE.	① NO ELECTRICAL DISCONTINUITY OF 1 μs.	X	—
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → +85 °C TIME 30 → 30 min UNDER 5 CYCLES. (THE TRANSFERRING TIME OF THE CHAMBER IS 2-3 MINUTE.)	① CONTACT RESISTANCE: NO VARIATION OF 50 mΩ OR MORE FROM INITIAL VALUE. SHIELDING RESISTANCE: NO VARIATION OF 50 mΩ OR MORE FROM INITIAL VALUE.	X	—
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	② INSULATION RESISTANCE: 25 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY 48 h.	NO DEFECT SUCH AS CORROSION WHICH IMPAIRS THE FUNCTION OF CONNECTOR.	X	—
SULFUR DIOXIDE GAS		EXPOSED IN 10-15 PPM 96h.		X	—
RESISTANCE TO SOLDERING HEAT		① REFLOW TEMPERATURE: PEAK 250°C MAX, 240°C MIN :20 sec MAX 220°C MIN :60 sec MAX ② MANUAL SOLDERING TEMPERATURE: 350°C, 3sec MAX.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 230°C FOR INSERTION DURATION, 3 sec.	SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARKS			APPROVED	KH. IKEDA	14. 11. 06
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT			CHECKED	MH. TSUCHIDA	14. 11. 06
			DESIGNED	IO. DENPOUYA	14. 11. 06
Unless otherwise specified, refer to JIS C 5402, IEC60512.			DRAWN	YJ. HAGA	14. 10. 23
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC4-313271-03	
HRS	SPECIFICATION SHEET		PART NO.	DF36A-25S-0.4V (55)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL662-4011-4-55	△ 1/1