

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
Rating	Operating Temperature Range	-55 °C to +85 °C ⁽¹⁾	Storage Temperature Range	-10 °C to +60 °C ⁽²⁾	
	Operating Humidity Range	Relative humidity 85 % max (Not dewed)	Storage Humidity Range	Relative humidity 85 % max (Not dewed)	
	Voltage	200 V AC	Applicable Cable	—	
	Current	1 A	Insulation	—	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
General Examination		Visually and by measuring instrument.	According to drawing.	×	×
Marking		Confirmed visually.		×	×
ELECTRIC CHARACTERISTICS					
Contact Resistance		100 mA (DC or 1000 Hz).	15 mΩ MAX .	×	—
Insulation Resistance		500 V DC.	1000 MΩ MIN.	×	—
Voltage Proof		650 V AC for 1 min.	No flashover or breakdown.	×	—
MECHANICAL CHARACTERISTICS					
Mechanical Operation		100 times insertions and extractions.	1) Contact Resistance: 20 mΩ MAX. 2) No damage, crack and looseness of parts.	×	—
Vibration		Frequency 10 to 55 Hz, single amplitude : 0.75 mm, 2 h in 3 directions.	1) No electrical discontinuity of 1 μs. 2) No damage, crack and looseness of parts.	×	—
Shock		490 m/s ² , duration of pulse 11 ms at 3 times for 3 both axial directions.		×	—
ENVIRONMENTAL CHARACTERISTICS					
Damp Heat (Steady state)		Exposed at 40 ± 2 °C, 90 to 95 %, 96 h.	1) Contact Resistance: 20 mΩ MAX. 2) Insulation Resistance: 1000 MΩ MIN. 3) No damage, crack and looseness of parts.	×	—
Rapid Change of Temperature		Temperature -55 → +5 TO +35 → +85 → +5 TO +35 °C Time 30 → 10 TO 15 → 30 → 10 TO 15 min. Under 5 cycles.		×	—
Corrosion salt mist		Exposed in 5 % salt water spray for 48 h.	1) Contact Resistance: 20 mΩ MAX. 2) No heavy corrosion.	×	—
Sulphur Dioxide		Exposed in 10 PPM FOR 96 h. (Test standard: JEIDA 39)		×	—
Resistance to Soldering Heat		Reflow soldering :250 °C MAX, 220 °C MIN, for 60 s MAX Soldering irons : 360°C FOR 5 s MAX.	No deformation of case of excessive looseness of the terminals.	×	—
Solderability		Soldered at solder temperature, 245 ± 3 °C, for immersion duration, 3 s.	A new uniform coating of solder shall cover a minimum of 95 % of the surface being immersed.	×	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
①	1	DIS-F-00004353	HR.NAGAYASU	HT.YAMAGUCHI	20190301
REMARK (1)TEMPERATURE RISE INCLUDED WHEN ENERGIZED. (2)THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED. Unless otherwise specified, refer to IEC-60512. Clerical corrections. ①			APPROVED	KJ.KATAYOSE	20050105
			CHECKED	HS.OKAWA	20050105
			DESIGNED	KT.DOI	20050105
			DRAWN	KT.DOI	20050105
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELCX-082601-71-21
HRS	SPECIFICATION SHEET		PART NO.	A3A-*PA-2SV(71)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL621	① 1/1