

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C(NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C(NOTES 3)	
	OPERATING HUMIDITY RANGE	20% TO 80%(NOTES 2)	STORAGE HUMIDITY RANGE	40% TO 70%(NOTES 2)(NOTES 3)	
	VOLTAGE	30V AC	APPLICABLE CONNECTOR	DF56※-26P-0.3SD(##)	
	CURRENT	AWG#42:0.2A AWG#44:0.15A (NOTES 4) AWG#46:0.1A			
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	
MARKING		CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100m A (DC OR 1000 Hz).	CONTACT:80mΩ MAX. SHIELDING:80mΩ MAX.	X	—
INSULATION RESISTANCE		100V DC.	50MΩ MIN.	X	—
VOLTAGE PROOF		100V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION		20TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: NO VARIATION OF 50 mΩ OR MORE FROM INITIAL VALUE. SHIELDING RESISTANCE: NO VARIATION OF 50 mΩ OR MORE FROM INITIAL VALUE. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, 3 DIRECTIONS × 10 CYCLE.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		X	—
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 →+85 °C TIME 30 → 30 min UNDER 5 CYCLES. (THE TRANSFERRING TIME OF THE CHAMBER IS 2-3 MINUTE.)	① CONTACT RESISTANCE: NO VARIATION OF 50 mΩ OR MORE FROM INITIAL VALUE. SHIELDING RESISTANCE: NO VARIATION OF 50 mΩ OR MORE FROM INITIAL VALUE.	X	—
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	② INSULATION RESISTANCE: 25 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SULFUR DIOXIDE GAS		EXPOSED IN 10-15 PPM 96h.	NO DEFECT SUCH AS CORROSION WHICH IMPAIRS THE FUNCTION OF CONNECTOR.	X	—
RESISTANCE TO SOLDERING HEAT		①REFLOW TEMPERATURE: PEAK 250°C MAX 240°C MIN :20 sec MAX 220°C MIN :60 sec MAX ②MANUAL SOLDERING TEMPERATURE: 350°C, 3sec MAX.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 245°C FOR INSERTION DURATION, 5 sec. (Sn-3.0Ag-0.5Cu)	SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARKS			APPROVED	TS. SAKATA	11. 04. 01
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT			CHECKED	HS. OZAWA	11. 03. 31
NOTE2: NON CONDENSING			DESIGNED	AH. MIYAZAKI	11. 03. 31
NOTE3: THE TERM "STORAGE" REFERS TO PRODUCTS STORED FOR A LONG PERIOD PRIOR TO MOUNTING AND USE. THE OPERATING TEMPERATURE AND HUMIDITY RANGE COVERS THE NON-CONDUCTING CONDITION OF CONNECTORS AFTER BOARD MOUNTING AND THE TEMPORARY STORAGE CONDITIONS OF TRANSPORTATION, etc			DRAWN	AH. MIYAZAKI	11. 03. 31
NOTE4: TEMPERATURE RISE OF CONNECTOR BODY ONLY, AND THAT OF CASE IS NOT INCLUDED. Unless otherwise specified, refer to JIS C 5402,IEC60512.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-329549-01
HRS	SPECIFICATION SHEET		PART NO.	DF56C-26S-0. 3V (51)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL662-5603-9-51	△ 1/1