





COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				
△					△				




(20, 32, 40, 52, 60, 68, 80, 100 CONTACTS)




(26, 34, 50 CONTACTS)

RECOMMENDED PC BOARD HOLE PATTERN
(MOUNT SIDE)



(20, 32, 40, 52, 60, 68, 80, 100 CONTACTS)



(26, 34, 50 CONTACTS)

NOTE 1. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

PART No.	CODE No.	NUMBER OF CONTACTS	A	B	C
HIF6A- 20DA-1.27DSA(71)	CL631-0101-5-71	20	20.95	11.43	18.55
HIF6A- 26DA-1.27DSA(71)	CL631-0102-8-71	26	24.76	15.24	22.36
HIF6A- 32DA-1.27DSA(71)	CL631-0103-0-71	32	28.57	19.05	26.17
HIF6A- 34DA-1.27DSA(71)	CL631-0104-3-71	34	29.84	20.32	27.44
HIF6A- 40DA-1.27DSA(71)	CL631-0105-6-71	40	33.65	24.13	31.25
HIF6A- 50DA-1.27DSA(71)	CL631-0106-9-71	50	40.00	30.48	37.60
HIF6A- 52DA-1.27DSA(71)	CL631-0107-1-71	52	41.27	31.75	38.87
HIF6A- 60DA-1.27DSA(71)	CL631-0108-4-71	60	46.35	36.83	43.95
HIF6A- 68DA-1.27DSA(71)	CL631-0109-7-71	68	51.43	41.91	49.03
HIF6A- 80DA-1.27DSA(71)	CL631-0110-6-71	80	59.05	49.53	56.65
HIF6A-100DA-1.27DSA(71)	CL631-0111-9-71	100	71.75	62.23	69.35

1	PBT	BLACK	UL94V-0	2, 3	COPPER ALLOY	CONTACT AREA: GOLD 0.2μm min. DIP AREA: TIN 2μm min. UNDER PLATING: NICKEL 2.5μm min.
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD)	CL	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED

SCALE 2 : 1	DRAWING NO. EDC3-154272-21	PART NO. HIF6A-**DA-1.27DSA(71)
UNITS mm	CODE NO.	

HRS

HIROSE ELECTRIC CO., LTD