





Mar.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Applicable standard					
Rating	Operating Temperature Range	-55°C to +85°C (Note1)	Storage Temperature Range	-10 °C to +60°C (Note3)	
	Operating Humidity Range	20% to 80% (Note2)	Storage Humidity Range	40% to 70% (Note3)	
	Voltage	50 V AC/DC	Applicable Connector	DF53#-*P-0.6C	
	Current	1.3A/pin	Applicable cable	AWG32	
Insulation diameter			φ0.4mm MAX		
Specifications					
Item	Test method	Requirements	QT	AT	
Construction					
General Examination	Visually and by measuring instrument.	According to drawing.	X	X	
Marking	Confirmed visually.		X	X	
Electric Characteristics					
Contact resistance Millivolt level method	20mV MAX, 1mA (DC or 1000Hz).	40 mΩ MAX.	X	—	
Mechanical Characteristics					
Mechanical operation	20 times insertion and extraction.	1. Contact resistance: 40 mΩ MAX. 2. No damage, crack or looseness of parts.	X	—	
Vibration	Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 10 cycles for 3 direction.	1. No electrical discontinuity of 1μs. 2. No damage, crack or looseness of parts.	X	—	
Shock	500 m/s ² duration of pulse 11 ms at 3 times each for 3 both axial directions.	1. No electrical discontinuity of 1μs. 2. No damage, crack or looseness of parts.	X	—	
Rance tensile strength	Measuring the strength of fixing the housing and pulling the wire.	3 N MIN.	X		
Environmental Characteristics					
Damp Heat (Steady State)	Exposed at 40 ± 2°C , humidity 90 to 95 %, 96 h. (After leaving the room temperature for 1 to 2h.)	1. Contact resistance: 40 mΩ MAX. 2. No damage, crack or looseness of parts.	X	—	
Rapid Change Of Temperature	Temperature -55°C→ +85°C Time 30min→ 30min  Under 5 Cycles. (The transferring time of the tank is 2 to 3 MIN) (After leaving the room temperature for 1 to 2h.)	1. Contact resistance: 40 mΩ MAX. 2. No damage, crack or looseness of parts.	X	—	
Dry Heat	Exposed at 85±2°C, 96h		X	—	
Cold	Exposed at -55±3°C, 96h		X	—	
Remarks Note 1: Include the temperature rising by current. Note 2: No condensing. Note 3: Applicable to unused product packaging.					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	1	DIS-H-00019500	JN. TONAI	SZ. ONO	20231120
Unless otherwise specified, refer to IEC 60512.			APPROVED	SJ. OKAMURA	20210114
			CHECKED	TT. OHSAKO	20210114
			DESIGNED	TH. SATO	20210113
			DRAWN	TH. SATO	20210113
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-380643-00-00
	SPECIFICATION SHEET		PART NO.	DF53-32PCF	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0668-1025-0-00	 1/1