





APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	-55°C TO +85°C	STORAGE TEMPERATURE RANGE	-10°C TO +60°C			
	VOLTAGE	AC 50V	OPERATING HUMIDITY RANGE	RELATIVE HUMIDITY:90% MAX (NO DEW CONDENSATION IS PERMITTED)			
	CURRENT	SIGNAL: 0.5A					
SPECIFICATIONS							
ITEM		TEST METHOD		REQUIREMENTS		QT	AT
CONSTRUCTION							
GENERAL EXAMINATION		VISUAL AND WITH MEASURING INSTRUMENT		ACCORDING TO A DRAWING		X	X
MARKING		CONFIRM VISUALLY				X	X
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE [EIA-364-23]		100mA	50mΩ MAX (*1) (HEGHT:10 ~ 19mm) 60mΩ MAX (*1) (HEGHT:20 ~ 29mm) 70mΩ MAX (*1) (HEGHT:30 ~ 39mm) 80mΩ MAX (*1) (HEGHT:40 ~ 46mm)		X	—	
INSULATION RESISTANCE [EIA-364-21]		100V DC	1000MΩ MIN		X	—	
VOLTAGE PROOF [EIA-364-20]		150V AC FOR 1 min	NO FLASHOVER OR BREAKDOWN		X	—	
MECHANICAL CHARACTERISTICS							
INSERTION AND WITHDRAWAL FORCES [EIA-364-13]		MEASURED WITH RESPECT TO APPLICABLE CONNECTORS		REFER TO THE MATING SIDE STANDARD. 	X	—	
MECHANICAL OPERATION [EIA-364-09]		100 TIMES INSERTION AND EXTRACTION		1) CONTACT RESISTANCE CHANGE:20mΩ OR LESS 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS	X	—	
RANDOM VIBRATION [EIA-364-28]		FREQUENCY:50 TO 2000Hz POWER SPECTRAL DENSITY:0.1G <sup>2</sup> /Hz FOR 120 min IN 3 DIRECTIONS		1) NO ELECTRICAL DISCONTINUITY OF 1μs OR MORE 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS	X	—	
SHOCK [EIA-364-27]		490m/s <sup>2</sup> , DURATION OF PULSE:11ms 18 TIMES TOTAL, 3 EACH DIRECTION, 3 AXIS			X	—	
ENVIRONMENTAL CHARACTERISTICS							
THERMAL SHOCK [EIA-364-32]		TEMPERATURE(°C): -65 → 20 ~ 35 → 105 → 20 ~ 35 TIME(min): 30 → 5MAX → 30 → 5MAX UNDER 25 CYCLES		1) CONTACT RESISTANCE CHANGE:20mΩ OR LESS 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS	X	—	
CYCLIC TEMPERATURE AND HUMIDITY [EIA-364-31]		@ 25°C, 80% RH:60 min DWELL TIME ↓ 30 min RAMP TIME @ 65°C, 50% RH:60 min DWELL TIME UNDER 24 CYCLES			X	—	
DRY HEAT [EIA-364-17]		EXPOSED AT 105°C, 120 HOURS		1) CONTACT RESISTANCE CHANGE:20mΩ OR LESS 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS	X	—	
MIXED FLOWING GAS [EIA-364-65]		EXPOSED AT 30°C, 70% RH Cl <sub>2</sub> :10ppb, NO <sub>2</sub> :200ppb, H <sub>2</sub> S:10ppb, SO <sub>2</sub> :100ppb UNMATED 7 DAYS → MATED 7 DAYS		CONTACT RESISTANCE CHANGE:20mΩ OR LESS	X	—	
REFLOW TEMPERATURE CONDITION [IPC/JEDEC STD-020]		PRECONDITION AT 60°C, 60% RH FOR 120 HOURS REFLOW PEAK TEMPERATURE:260°C AT CONNETOR SURFACE		NO BLISTER OR EVIDENCE OF MELTING	X	—	
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE	
	1	DIS-F-00003665		TH.SANO	MK.EZAKI	18.08.09	
REMARK (*1) THE VALUE OF CONTACT RESISTANCE INCLUDES THE BULK RESISTANCE.				APPROVED	MK.EZAKI	16.04.15	
				CHECKED	YS.TAKEUCHI	16.04.15	
				DESIGNED	TH.SANO	16.04.15	
				DRAWN	TH.SANO	16.04.15	
NOTE QT: QUALIFICATION TEST; AT: ASSURANCE TEST; X: APPLICATION TEST				DRAWING NO.		ELC-354280-00-00	
	SPECIFICATION SHEET			PART NO.	IT8M-120P-BGA-0H		
	HIROSE ELECTRIC CO., LTD.			CODE NO.	CL636-3001-9-00	 1/1	