

Oct.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-35°C TO + 85°C (NOTE1)	STORAGE TEMPERATURE RANGE	-10°C TO + 60°C (NOTE3)
	OPERATING HUMIDITY RANGE	20 % TO 80 % (NOTE2)	STORAGE HUMIDITY RANGE	40 % TO 70 % (NOTE3)
	VOLTAGE	AC/DC 100V	APPLICABLE CONNECTOR	DF50A-*S-1C
	CURRENT	AWG 28 : 1.0 A AWG 30 : 0.9 A	APPLICABLE CONTACT	DF50-2830SCFA
SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	AC 20mV MAX 1mA (DC OR 1000 Hz).	30mΩ MAX.	X	—
INSULATION RESISTANCE	100V DC.	500MΩ MIN.	X	—
VOLTAGE PROOF	300V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	30TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 50mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 10 CYCLE FOR EACH, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	① CONTACT RESISTANCE: 50mΩ MAX. ② INSULATION RESISTANCE: 100MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→+85°C TIME 30→30min. UNDER 5 CYCLES. THE TRANSFERRING TIME OF THE TANK IS 2~3 min.	① CONTACT RESISTANCE: 50mΩ MAX. ② INSULATION RESISTANCE: 500MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△				
		APPROVED	KI. AKIYAMA	12. 06. 26
		CHECKED	HK. UMEHARA	12. 06. 26
		DESIGNED	ST. SATO	12. 06. 26
		DRAWN	ST. SATO	12. 06. 26
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test	DRAWING NO.	ELC4-346572-01	
HRS	SPECIFICATION SHEET	PART NO.	DF50A-*P-1H(51)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL665-	△ 1/2

