

Applicable standard					
Rating	Operating Temperature Range	-55 to +85°C (Note1)	Storage Temperature Range	-10 °C to +60°C (Note3)	
	Operating Humidity Range	20% to 80% (Note2)	Storage Humidity Range	40% to 70% (Note3)	
	Voltage	50 V AC/DC	Applicable Connector	DF53-10P-0.6C(##)	
	Current	All pin	AWG 32 : 0.7A		
Any of 2 pins as a power		AWG 32 : 1.3A(power), 0.5A(signal)			
Specifications					
Item		Test method	Requirements	QT	AT
Construction					
General Examination		Visually and by measuring instrument.	According to drawing.	X	X
Marking		Confirmed visually.		X	X
Electric Characteristics					
Contact Resistance		20mV MAX, 1mA (DC or 1000Hz).	20 mΩ MAX.	X	—
Insulation Resistance		100 V DC.	100 MΩ MIN.	X	—
Voltage Proof		200 V AC for 1 min.	No flashover or breakdown.	X	—
Mechanical Characteristics					
Mechanical Operation		20 times insertion and extraction.	1.Contact resistance: 40 mΩ MAX. 2.No damage, crack or looseness of parts.	X	—
Mating and unmating force		It takes out and inserts with a conformity connector.	1.Mating Force : 18.2N MAX. 2.Unmating Force : 3.1N MIN.	X	—
Vibration		Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 10 cycles for 3 direction.	1.No electrical discontinuity of 1 μ s. 2.No damage, crack or looseness of parts.	X	—
Shock		Acceleration 500 m/s ² duration of pulse 11 ms at 3 times for 3 directions.		X	—
Environmental Characteristics					
Damp Heat (Steady State)		Exposed at 40 ± 2°C , humidity 90 to 95 %, 96 h. (After leaving the room temperature for 1 to 2h.)	1.Contact resistance: 40 mΩ MAX. 2.Insulation resistance: 100 MΩ MIN. 3.No damage, crack or looseness of parts.	X	—
Rapid Change Of Temperature		Temperature -55°C→ +85°C Time 30min→ 30min Under 5 Cycles. (The transferring time of the tank is 2 to 3 MIN) (After leaving the room temperature for 1 to 2h.)	1.Contact resistance: 40 mΩ MAX. 2.Insulation resistance: 100 MΩ MIN. 3.No damage, crack or looseness of parts.	X	—
Dry Heat		Exposed at 85±2°C, 96h	1.Contact resistance: 40 mΩ MAX. 2.Insulation resistance: 100 MΩ MIN. 3.No damage, crack or looseness of parts.	X	—
Cold		Exposed at -55±3°C, 96h	1.Contact resistance: 40 mΩ MAX. 2.Insulation resistance: 100 MΩ MIN. 3.No damage, crack or looseness of parts.	X	—
Remarks Note 1: Include the temperature rising by current. Note 2: No condensing Note 3: Applicable to unused product packaging.					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	0				
Unless otherwise specified, refer to IEC 60512.			APPROVED	S.J. OKAMURA	20230829
			CHECKED	SZ. ONO	20230829
			DESIGNED	JN. TONAI	20230829
			DRAWN	JN. TONAI	20230829
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-380625-00-00
	SPECIFICATION SHEET		PART NO.	DF53-10S-0. 6H	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0668-1007-0-00	1/2

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Specifications					
Item	Test method	Requirements	QT	AT	
Resistance to soldering heat	« Reflow area » Number of cycles : 2 cycles MAX 250°C MAX 10 sec MAX 220°C MIN 60 sec MAX « Preheating area » 150°C to 180°C 90 sec to 120 sec	No deformation of case of excessive looseness of the terminals.	X	—	
Solderability	Soldered at solder temperature, 245°C for insertion duration, 5sec.	Solder shall cover a minimum of 95 % of the surface being immersed.	X	—	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC-380625-00-00		
	SPECIFICATION SHEET	PART NO.	DF53-10S-0. 6H		
	HIROSE ELECTRIC CO., LTD.	CODE NO	CL0668-1007-0-00		2/2