

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-40°C TO 85°C(NOTE 1)	STORAGE TEMPERATURE RANGE	-10°C TO 60°C
	VOLTAGE	30V AC/DC	APPLICABLE CONNECTOR	BM28B0. 6-40DP/2-0. 35V (**)
	CURRENT	SIGNAL CONTACT : 0. 3A POWER CONTACT : 5. 0A		
SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	20mV AC OR LESS 1kHz,1m A .	Signal contact resistance: 100 mΩ MAX. Power contact resistance: 30 mΩ MAX.	X	-
INSULATION RESISTANCE	100V DC.	50MΩ MIN.	X	-
VOLTAGE PROOF	100V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	-
MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	10TIMES INSERTIONS AND EXTRACTIONS.	① Signal contact resistance: 100 mΩ MAX. Power contact resistance: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
VIBRATION	FREQUENCY 10 TO 55 TO 10 Hz,APPROX 5min, SINGLE AMPLITUDE 0.75 mm,10CYCLES, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
ENVIRONMENTAL CHARACTERISTICS				
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → +85°C TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHANBER : WITHIN 2-3 min)	① Signal contact resistance: 100 mΩ MAX. Power contact resistance: 30 mΩ MAX. ② INSULATION RESISTANCE: 50MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	① Signal contact resistance: 100 mΩ MAX. Power contact resistance: 30 mΩ MAX. ② INSULATION RESISTANCE: 25MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
SULPHUR DIOXIDE	EXPOSED IN 25 PPM FOR 96h,25°C,75%. (REFER TO JIS C 60068)	① Signal contact resistance: 100 mΩ MAX. Power contact resistance: 30 mΩ MAX.	X	-
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△				
REMARKS		APPROVED	MO. ISHIDA	17. 01. 30
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT		CHECKED	TS. MIYAZAKI	17. 01. 30
Unless otherwise specified, refer to JIS C 5402 and IEC 60512.		DESIGNED	RT. SHIMIZU	17. 01. 27
		DRAWN	SN. NUMAZAKI	17. 01. 23
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC-363042-61-00	
HRS	SPECIFICATION SHEET	PART NO.	BM28B0. 6-40DS/2-0. 35V (61)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL673-5019-0-61	△ 1/1