

APPLICABLE STANDARD						
RATING	Operating Temperature Range	$\triangle 1$ -55°C to 85°C (Note 1)	Storage Temperature Range	-10°C TO 60°C		
	Voltage	$\triangle 1$ 50V AC/DC				
	Current	Signal contact : 0.3A Power contact : 2.0A				
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION						
General Examination		Visually and by measuring instrument.		According to drawing.	X	X
Marking		Confirmed visually.		According to drawing.	X	X
ELECTRIC CHARACTERISTICS						
Contact Resistance	20mV AC or less 1kHz,1m A .		Signal contact resistance: 50 mΩ MAX. $\triangle 1$ Power contact resistance: 20 mΩ MAX. $\triangle 1$		X	—
Insulation Resistance	100V DC.		1000 MΩ MIN.		X	—
Voltage Proof	150V AC for 1 min.		No flashover or breakdown.		X	—
MECHANICAL CHARACTERISTICS						
Mechanical Operation	30times insertions and extractions. $\triangle 1$		① Signal contact resistance: 50 mΩ MAX. $\triangle 1$ Power contact resistance: 20 mΩ MAX. $\triangle 1$ ② No damage, crack or looseness of parts.		X	—
Vibration	Frequency 10 to 55 Hz,approx 5min, Single amplitude 0.75 mm,10cycles, for 3 directions.		① No electrical discontinuity of 1 μs. ② No damage, crack or Looseness of parts.		X	—
Shock	490 m/s ² duration of pulse 11 ms at 3 times for 3 directions.		① No electrical discontinuity of 1 μs. ② No damage, crack or looseness of parts.		X	—
ENVIRONMENTAL CHARACTERISTICS						
Rapid Change of Temperature	Temperature -55 → +85°C Time 30 → 30 min Under 5 cycles. (Relocation time to chanber : within 2-3 min)		① Signal contact resistance: 50 mΩ MAX. $\triangle 1$ Power contact resistance: 20 mΩ MAX. $\triangle 1$ ② Insulation resistance: 1000MΩ MIN. ③ No damage, crack or looseness of parts.		X	—
Damp Heat (Steady state)	Exposed at 40 ± 2 °C, 90 to 95 %, 96 h.		① Signal contact resistance: 50 mΩ MAX. $\triangle 1$ Power contact resistance: 20 mΩ MAX. $\triangle 1$ ② Insulation resistance: 100MΩ MIN. ③ No damage, crack or looseness of parts.		X	—
Sulphur Dioxide	Exposed in 25 PPM for 96h,25°C,75%. (Refer to JIS C 60068)		Signal contact resistance: 50 mΩ MAX. $\triangle 1$ Power contact resistance: 20 mΩ MAX. $\triangle 1$		X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
$\triangle 1$	8	DIS-H-00019811	RT. SHIMIZU	TY. 001	20240122	
REMARKS			APPROVED	WR. FUKUCHI	20210423	
Note1: Include the temperature rising by current			CHECKED	TS. MIYAZAKI	20210423	
Unless otherwise specified, refer to JIS C 5402 and IEC 60512.			DESIGNED	RT. OSAKI	20210423	
			DRAWN	RT. OSAKI	20210423	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-378714-53-01	
HR	SPECIFICATION SHEET		PART NO.	BM29B0. 6-24DS/2-0. 35V (53)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0673-7053-0-53	$\triangle 1$	1/1