Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	Operating Temperature Range	-40°C to 85°C (Note 1)	Storage Temperature Range	-10°C TO 60°C
	Voltage	30V AC/DC	Applicable Connector	BM25-4S/2-V(**)
	Current ④	Signal contact : 0.3A Power contact : 10.0A		

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
General Examination	Visually and by measuring instrument.	According to drawing.	X	X
Marking	Confirmed visually.	According to drawing.	X	X
ELECTRIC CHARACTERISTICS				
Contact Resistance	20mV AC or less 1kHz,1m A .	Signal contact resistance: 30 mΩ MAX. Power contact resistance: 5 mΩ MAX.	X	–
Insulation Resistance	100V DC.	1000 MΩ MIN.	X	–
Voltage Proof	150V AC for 1 min.	No flashover or breakdown.	X	–
MECHANICAL CHARACTERISTICS				
Mechanical Operation	10 times insertions and extractions.	① Signal contact resistance: 30 mΩ MAX. Power contact resistance: 5 mΩ MAX. ② No damage, crack or looseness of parts.	X	–
Vibration	Frequency 10 to 55 to 10 Hz, approx. 5min, Single amplitude 0.75 mm,10cycles, for 3 directions.	① No electrical discontinuity of 1 μs. ② No damage, crack or Looseness of parts.	X	–
Shock	490 m/s^2 duration of pulse 11 ms at 3 times for 3 directions.	① No electrical discontinuity of 1 μs. ② No damage, crack or looseness of parts.	X	–
ENVIRONMENTAL CHARACTERISTICS				
Rapid Change of Temperature	Temperature -55 → +85℃ Time 30 → 30 min Under 5 cycles. (Relocation time to chamber : within 2-3 min)	① Signal contact resistance: 30 mΩ MAX. Power contact resistance: 5 mΩ MAX. ② Insulation resistance: 1000MΩ MIN. ③ No damage, crack or looseness of parts.	X	–
Damp Heat (Steady state)	Exposed at 40 ± 2 °C, 90 to 95 %, 96 h.	① Signal contact resistance: 30 mΩ MAX. Power contact resistance: 5 mΩ MAX. ② Insulation resistance: 100MΩ MIN. ③ No damage, crack or looseness of parts.	X	–
Sulphur Dioxide	Exposed in 25 PPM for 96h,25℃,75%. (Refer to JIS C 60068)	Signal contact resistance: 30 mΩ MAX. Power contact resistance: 5 mΩ MAX.	X	–

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
④	1	DIS-H-00001221	TR.YUNOKI	TS.MIYAZAKI	15.12.26

REMARKS
Note1: Include the temperature rising by current

Unless otherwise specified, refer to JIS C 5402 and IEC 60512.

APPROVED	KH.IKEDA	14.07.30
CHECKED	WR.FUKUCHI	14.07.30
DESIGNED	YK.KOBAYASHI	14.07.29
DRAWN	YK.KOBAYASHI	14.07.29

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

DRAWING NO. ELC4-358234-01

HRS	SPECIFICATION SHEET	PART NO.	BM25-4P/2-V(51)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL677-1201-2-51 ④	1/1

FORM HD0011-2-1