


圧着端子：圧着品質基準書
CRIMP CONTACT：CRIMP QUALITY STANDARD

製品名 PART NO.	DF60-8PCFA	コードNo. CODE NO.	680-3023-0-00
-----------------	------------	--------------------	---------------



項 目 CHECK POINT		寸 法 (mm) MEASURE (mm)	備 考 REMARKS
被覆位置 COVER LOCATION.	C	1. 5 MAX	
芯線先端位置 LOCATION OF TIP OF THE CORE.	D	0. 5 - 1. 5	
ベルマウス BELL-MOUTH.	E	0. 2 - 0. 9	
ベントアップ BENT-UP.	F	2° MAX	
ベントダウン BENT-DOWN.	G	5° MAX	
ツイスト TWIST.	H	± 2° MAX	
ローリング ROLLING.	I	± 3° MAX	
カットオフタブ CUT-OFF TAB.	J	0. 5 MAX	
ストリップ長 STRIP LENGTH.	K	6. 5 - 7. 5	圧着前でのストリップ長 Strip length prior to crimping.
圧着バリ高さ HEIGHT OF METAL CUT-OUT TEETH.		L	0. 1 MAX
ワイド WIDE.	圧着部 WIRE BARREL.	M	4. 80 MAX
	被覆部 INSULATION BARREL.	N	7. 80 MAX

注 1. アプリケーター調整の際は、必ずケーブルを使用して圧着形状を確認してください。
NOTE 1 To adjust applicator, please check the crimp condition (crimp height and configuration) by using cable.

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△ 1	DIS-H-00000715	TS. KUMAZAWA	TS. FUKUSHIMA	15. 07. 10
名 称 T I T L E			HRS ヒロセ電機株式会社 HIROSE ELECTRIC CO., LTD.	
DF60-8PCFA 圧着品質基準書			APPROVED	KI. AKIYAMA 14. 08. 28
DF60-8PCFA CRIMP QUALITY STANDARD			CHECKED	TS. FUKUSHIMA 14. 08. 28
			CHARGED	TS. KUMAZAWA 14. 08. 28
			WRITTEN	TS. KUMAZAWA 14. 08. 28
技 術 指 定 書 TECHNICAL SPECIFICATION			ATAD-H0797	△ 1 1