




May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Recommended panel cut out dimension



Mating figure



Note 1. Per Pack : 100 Pieces
2. UL (File No. E52653)
C-UL (File No. E52653)
TUV (Certificate No. R50244085) authorization article.




NO.		MATERIAL		FINISH . REMARKS		1	PBT	Gray . UL94V-0	
UNITS		SCALE		COUNT		DESCRIPTION OF REVISIONS		DESIGNED	CHECKED
mm		2 : 1		1		APPROVED : KI. AKIYAMA		15.07.06	15.07.03
HRS		HIROSE ELECTRIC CO., LTD.		CHECKED : TS. KUMAZAWA		15.07.03		DRAWING NO. EDC-363801-00-00	
				DESIGNED : TS. KUMAZAWA		15.07.03		PART NO. DF60R-2EP-10.16C	
				DRAWN : TS. KUMAZAWA		15.07.03		CODE NO. CL680-3053-0-00	
								1/2	


May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

DF60 IN-LINE TYPE RECOMMENDED PANEL MOUNTING MANUAL (WHEN NUTS USES)


NUT INSTALLATION PROCESS



1. SLIDE A NUT (SIZE:M3) TO NUT FIX PART.




2. PRESS DOWN THE NUT UNTIL IT CLICKS,
THEN THIS SOUND MEANS THE NUT HAS INSERTED
INTO NUT HOLDER.




PANEL MOUNTING PROCESS

1. INSERT CONNECTOR INTO PANEL CUT OUT PART.



2. TIGHTEN A SCREW (SIZE:M3) TO FIX WITH PANEL.
RECOMMENDED TORQUE : LESS THAN 49N · cm



HRS

DRAWING NO.	EDC-363801-00-00
PART NO.	DF60R-2EP-10.16C
CODE NO.	CL680-3053-0-00

2/2