







APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	 -55°C TO 85°C (NOTE 1)	STORAGE TEMPERATURE RANGE	-10°C TO 60°C		
	VOLTAGE	 50V AC/DC	MATING CONNECTOR	DF40*-24DP-0. 4V (**)		
	CURRENT	0. 3A				
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.			X	X
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		20mV AC OR LESS 1kHz,1mA .		90mΩ MAX.	X	—
INSULATION RESISTANCE		100V DC.		50MΩ MIN.	X	—
VOLTAGE PROOF		150V AC FOR 1 min. 		NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS						
MECHANICAL OPERATION		30TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 90mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
VIBRATION		FREQUENCY 10 TO 55 TO 10 Hz,APPROX 5min, SINGLE AMPLITUDE 0.75 mm,10CYCLES, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
ENVIRONMENTAL CHARACTERISTICS						
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → 85°C TIME 30 → 30 min UNDER 5 CYCLES.		① CONTACT RESISTANCE: 90mΩ MAX. ② INSULATION RESISTANCE: 50MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.		① CONTACT RESISTANCE: 90mΩ MAX. ② INSULATION RESISTANCE: 25MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SULPHUR DIOXIDE		EXPOSED IN 25 PPM FOR 96h,25°C,75%.		① CONTACT RESISTANCE: 180mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
HEAT RESISTANCE OF SOLDERING		RECOMMENDED TEMPERATURE PROFILE SOLDERING AREA MAX 250°C, 220°C FOR 60 SECONDS MAX. PREHEATING AREA 150 TO 180°C 90 TO 120SECONDS. MAXIMUM TWICE ACTION IS ALLOWED UNDER THE SAME CONDITION. RECOMMENDED MANUAL SOLDERING CONDITION SOLDERING IRON TEMPERATURE 350°C. SOLDERING TIME: WIHTIN 3 SECONDS.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—
SOLDERABILITY		SOLDERING TEMPERATURE: 245±5°C DURATION OF IMMERSION: SOLDERING FOR 3 ±0.5 SECONDS.		A NEW UNIFORM COATING OF SOLDER SHALL COVER MINIMUM OF 95% OF THE SURFACE BEING IMMersed.	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
	3	DIS-H-00019849	RT. SHIMIZU	TY. 001	20240228	
REMARKS NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT				APPROVED	WR. FUKUCHI	20180419
				CHECKED	TS. MIYAZAKI	20180419
				DESIGNED	SJ. WADA	20180419
				DRAWN	SN. NUMAZAKI	20180418
Unless otherwise specified, refer to JIS C 5402, IEC 60512.						
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-311338-58-00	
	SPECIFICATION SHEET		PART NO.	DF40C-24DS-0. 4V (58)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0684-4006-1-58		1/1