

Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	Operating Temperature Range	-55°C to 125°C(Notes 1)	Storage Temperature Range	-10°C TO 60°C	
	Voltage	30V AC/DC	Mating Connector	DF40T*-34DS-0. 4V (**)	
	Current	0. 3A			
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
General Examination		Visually and by measuring instrument.	① According to drawing.	X	X
Marking.		Confirmed visually.		X	X
ELECTRIC CHARACTERISTICS					
Contact Resistance		20mV AC or less 1kHz, 1mA.	① 90mΩ MAX.	X	—
Insulation Resistance		100V DC.	① 50MΩ MIN.	X	—
Voltage Proof		100V AC for 1 min.	① No flashover or breakdown.	X	—
MECHANICAL CHARACTERISTICS					
Mechanical Operation		10times insertions and extractions.	① Contact resistance: 90mΩ MAX. ② No damage, crack or looseness of parts.	X	—
Vibration		Frequency 10 to 500, acceleration 49 m/s ² . Sweep time 1 oct/min. 8h for 3 axial directions.	① No electrical discontinuity of 1 μs. ② No damage, crack or looseness of parts.	X	—
Shock		Acceleration 980 m/s ² , duration of pulse 6 ms at 3 times for 3 directions.		X	—
ENVIRONMENTAL CHARACTERISTICS					
Rapid Change of Temperature		Temperature -55 → 125 °C Time 30 → 30 min Under 1000 cycles.	① Contact resistance: 90mΩ MAX. ② No damage, crack or looseness of parts.	X	—
Dry Heat		Exposed at 125 °C, 1,000 h.		X	—
Damp Heat		Exposed at 60 ± 2 °C Relative humidity 90 to 95 %, 1000 h.	① Contact resistance: 90mΩ MAX. ② Insulation resistance: 25 MΩ MIN. ③ No damage, crack or looseness of parts.	X	—
Damp Heat, Cyclic		Exposed at -10 to 65°C, Relative humidity 90 to 96%, 10cycles, total 240h.		X	—
Sulphur Dioxide		Exposed in 25 PPM for 96h, 40°C, Relative humidity 80%.	① Contact resistance: 180mΩ MAX.	X	—
Heat Resistance of Soldering		Recommended temperature profile soldering area MAX 250°C, 220°C for 60 seconds MAX. Preheating area 150 to 180°C 90 to 120 seconds. Maximum twice action is allowed under the same condition. Recommended manual soldering condition Soldering iron temperature 350°C. Soldering time: within 3 seconds.	① No deformation of case of excessive looseness of the terminals.	X	—
Solderability		Soldering temperature: 245 ± 5°C Duration of immersion: soldering for 3±0.5 seconds.	A new uniform coating of solder shall cover a minimum of 95% of the surface being immersed.	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△	7	DIS-H-00009674	YK. SATAKE	TS. MIYAZAKI	20210623
REMARKS			APPROVED	WR. FUKUCHI	20190424
Note1: Include the temperature rising by current			CHECKED	TS. MIYAZAKI	20190424
			DESIGNED	SJ. WADA	20190423
			DRAWN	SJ. WADA	20190423
Unless otherwise specified, refer to JIS C 5402. IEC 60512.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-386046-51-00
HRS		SPECIFICATION SHEET	PART NO.	DF40TC-34DP-0. 4V (51)	
		HIROSE ELECTRIC CO., LTD.	CODE NO.	CL0684-4255-0-51	△ 1/1