

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35°C TO 85°C(NOTE 1)	STORAGE TEMPERATURE RANGE	-10°C TO 60°C	
	VOLTAGE	30V AC	APPLICABLE CONNECTOR	BM14B (0. 8) -30DS-0. 4V (**)	
	CURRENT	0. 3A			
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	
QT		AT			
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	
MARKING		CONFIRMED VISUALLY.			
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		20mV AC OR LESS 1kHz,1mA .		100mΩ MAX.	
INSULATION RESISTANCE		100V DC.		50MΩ MIN.	
VOLTAGE PROOF		100V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION		10TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 100mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	
VIBRATION		FREQUENCY 10 TO 55 TO 10 Hz,APPROX 5min, SINGLE AMPLITUDE 0.75 mm,10CYCLES, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → +85°C TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHANBER : WITHIN 2-3 min)		① CONTACT RESISTANCE: 100mΩ MAX. ② INSULATION RESISTANCE: 50MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.		① CONTACT RESISTANCE: 100mΩ MAX. ② INSULATION RESISTANCE: 25MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	
SULPHUR DIOXIDE		EXPOSED IN 25 PPM FOR 96h,25°C,75%. (REFER TO JIS C 60068)		① CONTACT RESISTANCE: 100mΩ MAX. ② NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	
				CHECKED	
				DATE	
REMARKS				APPROVED	
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT				MO. ISHIDA	
				CHECKED	
				TS. MIYAZAKI	
				DESIGNED	
				NY. YAMASHIRO	
Unless otherwise specified, refer to JIS C 5402 and IEC 60512.				DRAWN	
				SN. NUMAZAKI	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-319848-53-00
HRS	SPECIFICATION SHEET			PART NO.	
	HIROSE ELECTRIC CO., LTD.			BM14B (0. 8) -30DP-0. 4V (53)	
			CODE NO.		CL684-8013-9-53
					△ 1/1